



GE  
Lighting

93348 - null

LED7DP203W830/35

Product Photo



#### GENERAL CHARACTERISTICS

Product Technology	LED
Rated Life (Hours)	25000 h
Base	E26

#### PHOTOMETRIC CHARACTERISTICS

Beam Spread (range)	35 deg
Center Beam Candle Pwr Candela	1200 cd
Nominal Initial Lumen per Watt	74.3
Rated Beam Spread	35 deg
Initial Lumens-nominal	520 lm
Color Rendering Index-CRI	80
Color Temperature	3000 K

#### PRODUCT INFORMATION

Product Code	93348
Description	LED7DP203W830/35
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168933483
Standard Package GTIN	00043168933483
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	043168933483
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168933483
Standard Package GTIN	10043168933480
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168933483

#### DIMENSIONS

Bulb Max Overall Length-MOL	3.5 in
-----------------------------	--------