

## 3 LED - w/o bracket (6.9 in) in textured white 15735WHT30 (Textured White)

Project Name: \_\_\_\_\_  
Location: \_\_\_\_\_  
Type: \_\_\_\_\_  
Qty: \_\_\_\_\_  
Comments: \_\_\_\_\_



### Dimensions

Height	0.75"
Length	7.00"
Width	0.75"

### Ordering Information

Product ID	15735WHT30
Finish	Textured White
Available Finishes	AZT, BBR, CO, GRY, SD, WHT

### Photometrics

Kelvin Temperature	3000K
--------------------	-------

### Specifications

Material	Aluminum
----------	----------

### Electrical

Voltage	12VAC/VDC
Operating Voltage Range	9-15 VAC/VDC
Lead Wire Length	70"

### Qualifications

Safety Rated	Wet
Expected Life Span	40000 Hours
Warranty	<a href="http://www.kichler.com/warranty">www.kichler.com/warranty</a>

### Primary Lamping

Light Source	LED
Lamp Included	Integrated
Number of Lights/LEDs	3
Max or Nominal Watt	.81W

#### Notes:

- 1) Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions.
- 2) Incandescent Equivalent: The incandescent equivalent as presented is an approximate number and is for reference only.