




**CATALOG NUMBER:** See table below  
**DESCRIPTION:** 6/3 & 8/1 SEOW, 125/250V 50A outdoor use cord set with "California Standard" twist-to-lock plug and cord connector

**CONSTRUCTION PARAMETERS:**

Conductors: (3) 6 AWG, 96/26 bunched bare copper  
 (1) 8 AWG, 96/28 bunched bare copper  
 Jacket material: TPE, black  
 Overall cable O.D. (nom): 0.868"



CS6364L

CS6365L

Plug and connector manufacturer: Hubbell Wiring Device  
 Plug and connector configuration: 50A 125/250V 3 pole 4 wire grounding, non-NEMA "California Standard"  
 Plug and connector materials: Nylon body and backshell  
 Neoprene cord gasket  
 Stainless steel plug shroud

**PROPERTIES:**

Temperature rating of cable: -40 to +90 deg C  
 Electrical ratings: 125/250 VAC, 50A

Length	Catalog number
25 ft	01937
50 ft	01918
100 ft	01919

The information presented here is, to the best of our knowledge, true and accurate. However, since conditions of use are beyond our control, all recommendations or suggestions are presented without guarantee or responsibility on our part.

We disclaim all liability in connection with the use of information contained herein or otherwise.

This specification is the proprietary intellectual property of Southwire Company, LLC. Any information contained herein shall not be disclosed to any party without the written consent of Southwire Company, LLC.