



Powering Business Worldwide

pe.eaton.com

BR style 1-inch commercial loadcenter

3BR1224N125

UPC:786676443159

Dimensions:

- **Height:** 21 IN
- **Length:** 3.88 IN
- **Width:** 14.31 IN

Notes:The maximum rating of the panel is the main breaker rating when used as service entrance equipment. Has notch for brhdk125 hold-down kit.

Warranties:

- 10 year

Specifications:

- **Special Features:** No feed-thru lugs, includes BREQS125 hold-down screw
- **Type:** Convertible main
- **Amperage Rating:** 125A
- **Box Size:** C1
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 10 kAIC
- **Main Circuit Breaker:** BR
- **Mounting:** Combination
- **Number Of Circuits:** 24
- **Number Of Spaces:** 12
- **Number Of Wires:** Four-wire
- **Phase:** Three-phase
- **Used With:** Type BR 1-inch breakers
- **Voltage Rating:** 208Y/120 or 240V
- **Wire Size:** Depends upon main breaker kit or main lug kit chosen.



Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Type BR 3-Phase Loadcenters](#)
- [3-Phase Loadcenter Program](#)

Certifications:

- UL 50
- UL 67

Product compliance: No Data