



Powering Business Worldwide

pe.eaton.com

Heavy Duty Safety Switch

DH221NRK

UPC: 782113205359

Dimensions: 16.5 IN * 9.12 IN * 8.31 IN (L * W * H)

Notes: 3-Phase hp ratings shown are grounded B phase ratings; UL listed

Warranty: Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Single-Throw
- **Amperage Rating:** 30A
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Painted galvanized steel
- **Fuse Class Provision:** Class H fuses
- **Fuse Configuration:** Fusible with neutral
- **Number Of Poles:** Two-pole
- **Number Of Wires:** Three-wire
- **Product Category:** Heavy Duty, Fusible with neutral
- **Voltage Rating:** 240V
- **Max Hp Rating:** 1.5 at 240 Vac Std. 1 Ph, 3 at 240 Vac Std. 3 Ph, 3 at 240 Vac TD 1 Ph, 7.5 at 240 Vac TD 3 Ph, 5 at 250 Vdc

Supporting documents:

- [Eaton's Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - DH221NRK](#)

Certifications: No Data

Product compliance: No Data

