

Item #: 6542-77	UPC Code: 747396076911
Product Family Name: City Square	Finish: CHROME
Category: Bath	Category Type: Bath
Certification 3057374	
Patents	
Notes:	



Image File Name:
 6542-77--
 1377127482.jpg



MEASUREMENTS

Width: 12.25	Length: 7	Height: 5	Extension: No
Height Adjustable: No	Min Overall Height:	Max Overall Height:	Slope: No
Wire Length: 7"	Chain Length:	Safety Cable Included: No	Net Weight: 18.25
Canopy Width: 0.63	Canopy Height: 4.50	Canopy Length: 6.00	
Backplate Width: 0.63	Backplate Height: 4.50	Center to Top: 5.00	Center to Bottom: 2.13

LAMPING

No. of Bulbs: 2	Light Type: A-19,Med			
Max Bulb Wattage: 100	Socket: E26,Med			
Dimmable: Yes	Ballast:	Rated Life Hours:	Photocell Included:	Lamps Included: No
Lamp Included: No	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:

SHADE / GLASS

Description:	Material: Glass
Part No.: G6541	Quantity: 2
Width: 3.75	Height: 5.38
	Length:



SHIPPING

Carton Width: 6.500	Carton Height: 9.500	Carton Length: 13.500
Carton Weight: 4.950	Carton Cubit Feet: 0.482	Small Package Shippable: Yes
Master Pack Width: 14.000	Master Pack Height: 20.250	Master Pack Length: 20.250
Master Pack Weight: 31.570	Master Cubic Feet:	Multi-Pack: 6



Damp Location
Yes



Title 17
Yes



ETL Intertek
Yes