



Hoffman

Lay-In NEMA Type 1 Galvanized Wireway Straight Section

Catalog Number: F44T172GV
US List Price (USD): \$64.87

Bulletin Number:

- F40G

Material:

- Steel



Model Code:

- 88220

Ship Wt. Std. Pkg. (lbs):

- 24.0

Interchangeable:

- False

Description

Description:

Available in lengths from 12.00 in. (305 mm) to 120.00 in. (3048 mm), with or without knockouts.

Technical Data

Lay-In NEMA Type 1 Galvanized Wireway Straight Section

Catalog Number	F44T172GV
A in.	4
B in.	4
C in.	72
F in.	---
X in.	---
Y in.	---
Number of Knockouts .50 in.-.75 in.	—
Number of Knockouts 1.00 in.-1.25 in.	---

Certifications



EU Certification



UL Certification

Documents



Spec Sheet



2D DXF CAD



3D STEP CAD



Dimension Drawing

No accessories available.