

IPX12-70Z



UPC Code: 07847728241

Country Of Origin: China

IPX12-70Z

Brand Features

Leviton offers many products that will help lower electrical costs and add convenience to everyday living. Simply replacing standard switches with dimmers reduces energy consumption and extends bulb life. IllumaTech Preset Dimmers and Fan Speed Controls feature a low-profile fluid slide bar movement for fine adjustment of light levels or fan speeds that's accompanied by an easy-to-use ON/OFF preset push button switch. The switch provides quick ON/OFF control without disturbing your favorite pre-selected settings. Models are available for incandescent, LED, CFL, magnetic or electronic low-voltage, Mark 7 and Mark 10 Powerline dimming-ballast fluorescent lighting, and quiet and standard fan speed control.

Item Description

1200VA-277VAC 60Hz, Single-Pole &3-Way, IllumaTech Fluorescent Dimmer for Mark 10 Powerline Ballasts, No LED; neutral required. White face assembled on device, Ivory and Light Almond color change kits included.

Technical Information

Product Features

Action: Standard ON/OFF

Warranty: 5-Year Limited

Preset: Preset

Color: White Ivory Light Almond

Switch Type: Single-Pole & 3-Way

Color Change Kit: IPKIT Series

Load Type: Electronic Mark 10 Powerline Fluorescent

Wallplate: Order Separately

Available Color Kits: Ivry-I Wht-W Gry-G Blk-E Brwn-B Light Almond-T, R-Red

Type: Electro-Mechanical

Load Rating: 1200VA

Voltage: 277 Volt AC 60Hz

Style Name: IllumaTech

Ordering Notes: Incl White, Ivory and Light Almond Color Kit

Standards and Certifications: UL/CSA/NOM

Protection: Radio/TV Filter

Features and Benefits

- Fluid slide movement allows fine adjustment of light level with minimum effort
- Easy-to-use push button switch
- Attractive styling coordinates perfectly with Leviton's complete line of Decora wiring devices
- Provides single pole and multi-location lighting control when used with a 3-way switch
- Built-in radio/TV interference filter
- Neutral Required

SPECIFICATION SUBMITTAL

JOB NAME: <input type="text"/>	CATALOG NUMBERS: <input type="text"/>	
JOB NUMBER: <input type="text"/>	<input type="text"/>	<input type="text"/>

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Teléfono: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): +1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2012 Leviton Manufacturing Co., Inc. Todos los derechos reservados. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

www.leviton.com/international/contacts/

