



S8158

FC40T5/830
40 watt; T5; Circline Fluorescent; 3000K Warm White; 82 CRI;
2GX13 (4-Pin) base

Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards



S8158

Item Number	Product Line	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code
S8158	HyGrade	045923081583	40	T5	2GX13	2GX13	FC40T5/830

MOD In Inches	MOL In Inches	Nominal Length	Nominal Diameter	Initial Lumens	Mean Lumens	Average Rated Hours	Kelvin Temp
0.63"	12"	12"	12"	3300	3350	12000	3000

Color	Pack	Package Type	CRI	Hg Content	RoHS Compliant
Warm White	12	Box	82	4.3 mg	Yes



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

