

BREAKER 200A 2P 120/240V 10K QNR



## General technical data

|                           |                         |
|---------------------------|-------------------------|
| Number of poles           | 2                       |
| Suitability for operation | Electrical Distribution |

## Electricity

|  |       |
|--|-------|
| Continuous current rated value                     | 175 A |
| Voltage between phase and Ground (GND) rated value | 120 V |
| Voltage between phase and phase rated value        | 240 V |

## Model

|                               |         |
|-------------------------------|---------|
| product brandname             | SIEMENS |
| Type of electrical connection | PLUG-IN |

## Mechanical Design

|                                |                  |
|--------------------------------|------------------|
| Depth [in]                     | 9 in             |
| Design of the overload release | Thermal Magnetic |
| Design of the product          | HQSH             |
| Height [in]                    | 3 in             |
| Width [in]                     | 6 in             |

## General product approval

---

Standard

UL 489

**last modified:**

02/22/2017