



S9456

18PAR38/LED/40'/4000K/120V/D
 18 watt PAR38 LED; 4000K; 40' beam spread; Medium base;
 120 volts

Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- IP65 - Wet location rated
- Approved for enclosed fixtures
- For Indoor and Outdoor use
- Dimmable

Compatible Dimmers

- Cooper TAL06P-C1
- LeGrand ADTP703TU
- Leviton 6674
- Lutron C.L. Family - Gen. 2.0 or above
- Lutron MACL-153M
- Lutron NTCL-250
- Lutron PD-6WCL
- Lutron SELV-300P



S9456

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S9456	045923094569	120	18	100W	PAR38	Medium	E26
Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
18PAR38/LED/40'/4000K/120V/D	Dimmable	Silver	5-3/16"	4-3/4"	1400	25000	4000
Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant	Fixture Type
Cool White	80	40	12/6	Box	ENERGY STAR	Yes	Enclosed Rated
UL or ETL Listed	UL Classification	Warranty					
Yes	cULus - Wet Location Rated	3 Year Limited					



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

