



- Lamps
- Ballasts
- Luminaires
- Company
- Customer Care
- Contact Us

Search > Results for F58T8/840 > F58T8/840 **35179** F58 T8 4000K 85CRI PROLUME



F58T8/840 35179 F58 T8 4000K 85CRI PROLUME

Product Number: 35179
 UPC: 807154351794

[Log In for Price and Availability](#)

Note: this product is only sold in multiples of 25 items

Specifications	Resources	Technical
Applications	office, building, school, manufacturing facilities	
Average Life (Hrs)	24000	
Base	Medium Bi-Pin	
Brand	ProLume	
Bulb	T8	
CRI	86	
Color Temperature	4000	
Design Lumens	5000	
Dimmable	No	
HTS code	8539310070	
Initial Lumens	5300	
Input Frequency (Hz)	60	
Markets	Residential, Commercial	
Master Carton Quantity	25	
Maximum Overall Diameter	1	
Maximum Overall Length	60	
Nominal Length	60	
Operating Position	Universal	
Prod Code	F58T8/840	
Product Category	Linear Fluorescent	
Product Description	F58 T8 4000K 85CRI ECO PROLUME	
Product Number	35179	
Start Type	Instant/Programmed Start	
Warranty (Yrs)	2	
Wattage (W)	58	

Substitute Items:



F58T8/840 109374 F58 T8 4000K 85CRI PROLUME

Products

Lamps



Ballasts



Luminaires



Resources

- Catalogs
- Sell Sheets
- New Products

Contact Us

Corporate Office:
Halco Lighting Technologi
2940 Pacific Drive
Norcross, GA 30071
Toll Free: 800.677.3334
Office: 770.242.3612
Fax: 800.880.0822
Email: [customer@hal](mailto:customer@halco.com)



Copyright © 2017 - Halco Lighting Technologies

- [Home](#)
- [News](#)
- [About Us](#)
- [FAQ](#)
- [Site Map](#)
- [Privacy P](#)