



Powering Business Worldwide

pe.eaton.com

A200/B100 Heater

FH17

UPC:786678629384

Dimensions:

- Height: X
- Length: X
- Width: X

Notes:Select heater coils based on full load current(FLA) shown on motor nameplate. Heater coils are rated to protect 40 degree C rise and a service factor of 1.15, Single-Phase requires 2 heaters, Three-Phase Requires 3 heaters

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Special Features:** Used with Starter Sizes 0,1, and 2
- **Type:** A200/B100 Heater
- **Design:** NEMA
- **Full Load Current Range:** Ambient 1.01-1.11, 1.17-1.28A, Non-Comp .94-1.03, 1.14-1.25A
- **Overload Relay:** Type A and B
- **Trip Type:** Thermal and Fast Trip

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [Instructions for A200, A210, A250 size 6, two- or three-pole non-reversing or reversing motor controllers](#)
- [Eaton Specification Sheet - FH17](#)

Certifications:

- CSA Certified



- UL Listed

Product compliance: No Data

© 2016 Eaton. All rights reserved.