



GE  
Lighting

21259 - null

LED165/M400/740

Product Photo



#### GENERAL CHARACTERISTICS

Product Technology	LED
Rated Life (Hours)	50000 h
Base	EX39

#### PHOTOMETRIC CHARACTERISTICS

Beam Spread (range)	0 deg
Initial Lumens-nominal	20000 lm
Color Rendering Index-CRI	73
Color Temperature	4000 K

#### PRODUCT INFORMATION

Product Code	21259
Description	LED165/M400/740
Alternative Unit Of Measure	EACH
Standard Package Quantity	3
Ean UPC	043168212595
Standard Package GTIN	00043168212595
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	3
Sales Unit	Each
UCC	043168212595
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168212595
Standard Package GTIN	10043168212592
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168212595

#### DIMENSIONS

Bulb Max Overall Length-MOL	11.42 in
-----------------------------	----------