



*max overall height

Measurements:

<u>Height</u>	<u>Width</u>	<u>Length</u>
16.50"	18.00"	51.50"
<u>Max OAH</u>	<u>Min OAH</u>	
140.50"	18.00"	
<u>Hanging Weight</u>	<u>Canopy Width</u>	
42.25 lb	18.00"	

Lamping:

LED G4 LED	2,304 Rated Lumens
24 1.5W G4 LED	3000 Color Temperature
36 total watt	30,000 Rated Life 80+ CRI
Dimmable : Electronic Low Voltage (ELV) dimmer	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
52.25 lb	21.50"	10.75"	72.50"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	845094060987	No	

Finish:

Polished Chrome PC

Glass:

Clear 18

Material:

Glass

Certification:

Dry Location

Additional:

G4 LED (Included)
Adjustable