

## ispot® LED Floodlights



### Description

The ispot® is the most advanced LED floodlight on the market, with an attractive ultra thin design and innovative high voltage LED chips. Suitable for use both indoors and outdoors and available in both white and black finishes.

### Features

- Innovative high voltage LED chips – no driver required
- Daylight (5700K) and Warm White (3000K) options
- High grade aluminium body and toughened glass lens
- Available in black and white finishes
- Complete with mounting bracket and 900mm flex
- Instant start and restart – can be used with PIR sensors
- 36,000 hours rated life
- 2 year guarantee

### Range

ispot® 10W 5700K WH	I1010W
ispot® 10W 5700K BK	I1010B
ispot® 10W 3000K WH	I1011W
ispot® 10W 3000K BK	I1011B
ispot® 20W 5700K WH	I1020W
ispot® 20W 5700K BK	I1020B
ispot® 20W 3000K WH	I1021W
ispot® 20W 3000K BK	I1021B

### Dimensions (mm), Beam Angle & Lumens

	Lumen Output	Beam Angle	Fitting Dimensions (L x H x D)
I1010	680lm	105°	152 x 130 x 25
I1011	640lm	105°	152 x 130 x 25
I1020	1200lm	100°	213 x 180 x 28
I1021	1200lm	100°	213 x 180 x 28

### Technical Specification

Voltage		230V~
		50/60Hz
Lamp		SMD LED
Colour	I1010/20	5700K
temp.	I1011/21	3000K
Beam	10W	105°
angle	20W	100°
IP rating		IP65

### Standards

- BS EN 60598-1+A11
- BS EN 60598-2-1
- BS EN 60598-2-5
- BS EN 62471
- BS EN 62493
- BS EN 55015+A2
- BS EN 61547
- BS EN 61000-3-2+A2
- BS EN 61000-3-3

Brackenheath  
2-8 Laporte Way, Luton  
Bedfordshire England  
LU4 8RJ

Email: [sales@brackenheath.co.uk](mailto:sales@brackenheath.co.uk)

Tel: +44 (0)1582 544590

Fax: +44 (0)1582 544591