



**71421  
LED Floodlight**



<b>Model :</b>		<b>71421</b>
OVERALL LAMP PARAMETERS	Input Voltage	100-277VAC 50/60HZ
	Input Current	0.5A Max @120V .2A Max @ 277V
	Input Power	30W
	Power Factor	PF≥0.95
	Luminance	2000 LM
	Luminous Efficiency	65 LM/W
	CRI	>70
	Beam Angle	180°
	Main Structure	Aluminium + Polycarbonate
LED DRIVER	Output Voltage	12-24 VDC
	Output Current	0.9A
	Driver Efficiency	88%
LED	LED Manufacturer	XBD
	LED Type	
	LED Quantity	18 PCS
	LED Efficacy	110 LM/W
	Color Temperature	WW/NW/CW (5000K)
Photocell	-	No
LIFESPAN & ENVIRONMENT	Lifespan	50000 Hrs.
	Warranty	5 Years
	IP Rating	IP54 Wet Locations
	Operating Temperature	-40F to 131F
	Storage Temperature.Humidity	-40°C—+80°C , 10—90% RH
SAFETY&EMC	Safety Norms	UL1598,UL8750, EN60598, EN61347-2-13, EN62031, EN62471
	Withstand Voltage	IIP-FG: 2121VDC
	Grounding Resistance	25A 100mΩ
	Electromagnetic Compatibility	EN55015, EN61000-2-3, EN61000-3-3, EN61547
OTHERS	Dimension	Pls refer to attached dimension drawing
	Net Weight	0.6KG
	Gross Weight	0.8KG
	Qty / Carton紙箱	12PCS
	Volume	0.52Cbm/carton
	Housing Color	White

Dimension :

71421

