



SURECRIMP® ALND ALUM 2 HOLE LONG BARREL



- Manufactured from high strength aluminum alloy which offers maximum conductivity and excellent crimping characteristics.
- Electro-Tin plated for low contact resistance.
- Chamfered entry for easy conductor insertion.
- Color coded end cap identifies the proper compression die.
- Roll marked barrel for easy identification and proper location of crimps.
- Pre-filled with DE-OX prevents oxide from forming.
- Dual rated for Aluminum or Copper conductors.
- UL 486A/B 90° C Listed and CSA Certified.
- If proper high voltage spacing and insulation techniques are used, may be used for high voltage applications up to 35KV.
- Expanded wire size applicable when installed with specified dieless tools.
- UL File E6207

Item ID	Conductor Size	Expanded Conductor	Bolt/Stud Size	Mounting Hole	Mounting Hole	Tang Length	Tang Width	Barrel Length	Strip Length	Overall Length	Color Code	Die Index Number	Die Catalog	Outside Diameter	Inside Diameter	Standard Package	NAED/UP C Number
ALND-1/0-38-1	1/0 AWG	1/0-1 AWG	3/8	0.4060	1	1.9870	0.8190	1.0700	1.1325	3.5000	TAN	296	ILD-296	0.5990	0.3850	10	0783669690668