



8822-12: One Light Outdoor Wall Lantern



Collection: Brentwood

Black Powdercoat Cast Aluminum Outdoor Wall Lantern with Clear Glass. Long Molded Panels.

Rugged but decorative cast aluminum. Outdoor wall lantern made with durable black powdercoat finish over cast aluminum and Clear Glass.

UPC #:785652882227

Finish: Black (12)

Dimensions:

Width: 7" **Extends:** 7"
Height: 10 1/4" **Wire:** 6 1/2" (color/Black/White)
Weight: 2.5 lbs. **Mounting Proc.:** Center Lock-Up
Connection: Mounted To Box
Bulb Appearance: Clear

Bulbs:

1 - Medium A19 60w Max. 120v - Not included
 1 - LED Medium A19 8w Max. 120v - Not included
 1 - LED Medium A19 13.5w Max. 120v - Not included

Features:

- Clear bulb(s) recommended for this fixture
- Easily converts to LED with optional replacement lamps
- Powder coat added to the finish to protect against aging.
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

Material List:

1 Canopy - Die Cast Aluminum - Black
 1 Cap - Die Cast Aluminum - Black
 1 Body - Die Cast Aluminum - Black

Safety Listing:

Safety Listed for Wet Locations
 Safety Listed for Wet Locations

Instruction Sheets:

Trilingual (English, Spanish, and French) (990W8822-BRE)

Shade / Glass / Diffuser Details:

| Part | Material | Finish | Quantity | Item Number | Length | Width | Height | Diameter | Fitter Diameter | Shade Top Length | Shade Top Width | Shade Top Diameter |
|-------|----------|--------|----------|-------------|--------|--------|--------|----------|-----------------|------------------|-----------------|--------------------|
| Panel | Glass | Clear | 6 | | | 2 3/16 | 5 3/4 | | | | | |

Backplate / Canopy Details:

| Type | Height / Length | Width | Depth | Diameter | Outlet Box Up | Outlet Box Down |
|------------|-----------------|-------|-------|----------|---------------|-----------------|
| Back Plate | 5 3/16 | 4 3/8 | 3/8 | | 6 | 4 1/4 |

Replacement Bulb Data:

| Product # | | | Type | Base | Watts | Watts Consumed | Volts | Hours | Lumens | Temp (°K) | CRI |
|-----------|---------|--|------|-------------|-------|----------------|-------|-------|--------|-----------|-----|
| 97308S | Frosted | | A19 | E-26 Medium | 8 | 8 | 120v | 50000 | 450 | 3000 | 85 |
| 97408S | Frosted | | A19 | E-26 Medium | 8 | 8 | 120v | 50000 | 450 | 2700 | 85 |
| 97309S | Frosted | | A19 | E-26 Medium | 13.5 | 13.5 | 120v | 50000 | 800 | 3000 | 85 |
| 97409S | Frosted | | A19 | E-26 Medium | 13.5 | 13.5 | 120v | 50000 | 800 | 2700 | 85 |

Shipping Information:

| Package Type | Product # | Quantity | UPC | Length | Width | Height | Cube | Weight | Fr. Class | UPS Ship |
|--------------|-----------|----------|-----|--------|-------|--------|------|--------|-----------|----------|
| | | | | | | | | | | |

| | | | | | | | | | | |
|-------------|---------|----|----------------|------|-------|-------|--------|------|-----|-----|
| Individual | 8822-12 | 1 | 785652882227 | 9.75 | 8.75 | 11.5 | 0.568 | 3.4 | 125 | Yes |
| Master Pack | | 3 | 10785652882224 | 27 | 10.25 | 12.25 | 1.962 | 11.9 | 125 | Yes |
| NJ Pallet | | 90 | | 48 | 40 | 66.25 | 73.611 | 357 | | No |
| NV Pallet | | 90 | | 48 | 40 | 66.25 | 73.611 | 357 | | No |