



S9674

54W/LED/HID/4000K/100-277V/EX39
 54 watt - LED HID Replacement; 4000K; Mogul extended base;
 100-277 volts

Features

- High Lumen Omni-directional LED for Industrial / Commercial applications
- Replaces HID, CFL, and Incandescent
- Ballast by-pass - Direct wire only 100V - 277V
- UL approved for totally enclosed fixtures
- Damp location - IP65 rated
- For outdoor & indoor use
- DLC Qualified
- Base up, base down or horizontal operation
- Emits no UV light / Contains no mercury (Hg)
- 5 year limited warranty
- Classified under UL 1598C

Additional Technical Specifications

- Power Factor >0.9
- Operating temperature range -20°C to 65°C
- Operating Frequency 50-60Hz
- Working Voltage AC90-305V

Minimum Compartment Size		
Length	Width	Depth
9.25 inch	9.25 inch	17.3 inch

Optional accessory: In-line surge protector [80-929](#)



S9674

Item Number	Product Line	UPC	Input Voltage	Watts	Incandescent Equivalent	Fluorescent Equivalent	HID Equivalent
S9674	Hi-Pro	045923096747	100 - 277	54	300W	85W	250W

Base	ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens
Mogul Extended	EX39	54W/LED/HID/4000K/100-277V/EX39	Non-Dimmable	White	10-3/4"	3.69"	7020

Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type
---------------------	-------------	-------	-----	-----------------	-----------------------	------	--------------

50000	4000	Cool White	80+	300	-20C (-4F) to a maximum of +65C (+149F)	12	Box
DLC ID:		RoHS Compliant	UL or ETL Listed	UL Classification	Warranty		
Search under: S9674A or PPU5E1Q6 or PWPMA3AA DLC Search		Yes	Yes	cULus - Damp Location Rated	5 Year Limited		



National Toll-Free:
 800.43.SATCO
 (800.437.2826)
www.satco.com

Distribution Centers:
 New York, Florida, Texas,
 Washington, California,
 Puerto Rico

Corporate Offices:
 110 Heartland Blvd.,
 Brentwood, NY 11717
 800.437.2826 631.243.2022
 Fax 631.243.2027

