



BURNDY Catalog Number

TP168F

UPC Number

7818107146833

Description

FORK- 22- 16 AWG- VINYL, 0.86

Status

IN L

Active

Web Use

BURNDY Product Line

Dimensional

Max Insulation Diameter

0.145

Length (in)

0.86

Tongue Type

Fork

Strip Length

13/64

Electrical

Max Voltage Rating

600

General

Product Description

Copper Terminal, Fork Tongue,
22-16 AWG, #6-#8 Stud, Vinyl
Insulated, Tin Plated

Other

Bulk Package

BA16EF8M

Physical

Type of Plating

Tin

Connector Type

Terminal - Fork

Color Code

Red

Insulation Type

Vinyl

Plated (Yes or No)

Y

Approvals / Certifications

UL Listed

Y

CSA Certified

Y

ROHS Compatible

Compliant

UL Recognized

N

CULUS

N

Conductor(s)

Copper Solid Size (Range)

N/A

Copper Stranded (Range)

20 AWG-16 AWG

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175