

TME19A

19" LED Monitor



Screen Size	19"
Aspect Ratio	5:4
Backlight System	LED
Max. Resolution	1280 x 1024
Viewing Angle	170°/160°
Brightness	250 cd/m ²
Contrast Ratio	1000:1
Response Time	5 ms
Power Supply	AC 120V-240V 50/60Hz
Power Consumption	23W
Input/Output	VGA DB 15pin HDMI BNC In and Out S-Video In Audio In / Output Jack
Speaker Output	1W + 1W
VESA Mountable	100mm x 100mm
Dimensions Without Base	16.4" x 2.3" x 14.3" (W x D x H)
Height With Base	16.4" x 6.8" x 16.8" (W x D x H)
Base Dimensions	10.7" x 7.1"
Weight	7.9 lb (net), 9.7 lb (gross)
Warranty	3 Year Limited

Specifications subject to change without notice.

