



### 31160-962: Three Light Chandelier



**Collection:** Oslo

**UPC #:**785652002946

**Finish:** Brushed Nickel (962)

#### Dimensions:

**Diameter:** 15"

**Height:** 16 1/2"

**Weight:** 6.2 lbs.

**Overall Height:** 139"

**Wire:** 144" (color/Clear)

**Chain:** 120"

**Mounting Proc.:** Center Lock-Up

**Connection:** Mounted To Box

#### Bulbs:

3 - Medium A19 100w Max. 120v - Not included

#### Features:

- Adjustable arms rotate for up or down lighting
- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.
- Supplied with wire pre-laced through chain

#### Material List:

1 Chain - Steel - Brushed Nickel

1 Body - Steel - Brushed Nickel

#### Safety Listing:

Safety Listed for Dry Locations

#### Instruction Sheets:

Trilingual (English, Spanish, and French) (HC-1901FS)

#### Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Cased Opal Etched	3				5 29/32	3 15/16				

#### Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	13/16			5 1/2		

#### Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	31160-962	1	785652002946	16.5	14	9	1.203	7.6	125	Yes
NJ Pallet		50		48	40	76	84.444	380		No
NV Pallet		50		48	40	76	84.444	380		No