



# S9721

15T8/LED/48-835/BP/120-277V  
 15 watt T8 LED; Medium bi-pin base; 3500K; 50000 average  
 rated hours; 1700 lumens



## Features

- No ballast or external driver required
- Direct wire 120-277V line voltage\*
- Single ended wiring; Non-shunted socket
- All glass tube
- -20°C (-4°F) to 45°C (113°F) - ambient operating temperature
- Long life: 50,000 hours
- cULus classified - Damp location
- 5 year warranty
- DLC listed

S9721

\* Install only in non-shunted lampholders

Item Number	UPC	Voltage	Watts	Operating Frequency	Fluorescent Equivalent	Lamp Shape	Base
S9721	045923097218	120-277	15	50/60Hz	25-32	T8	Medium Bi-Pin

  

ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
G13	15T8/LED/48-835/BP/120-277V	Non-Dimmable	Gloss White	48"	1.00"	1700	50000

  

Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	CEC Status	DLC ID:	RoHS Compliant
3500	Neutral White	82	230	10	Lawful for sale in California	PGMG5X1Y; PGNTWDHD <a href="#">DLC Search</a>	Yes

  

UL or ETL Listed	UL Classification	Warranty
Yes	cULus - Damp Location Rated	<a href="#">5 Year Limited</a>



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

