



Actual

Catalog Number: 703 2
Product ID: 7TAA005070R0029
UPC Number: 61601314372
Status: Active

Clamp, Universal, 14 Gauge, Size 2 Inch, Pipe Outer Diameter 2.195 Inches - 2.375 Inches, Steel, For use with Rigid or IMC Conduit, Pipe and Electrical Metal Tubing

- Square nut is captivated on the shoulder for easy one-handed tightening.
- Straps are interchangeable with 1-1/2 Inch strut, for broader application.
- Straps are shipped assembled so counting and sorting are easier.
- Pipe and conduit sizes are shown on the strap for easy identification.

North American Specifications (UNSPSC)

UNSPSC	31162906 Hose or pipe clamps
IGCC	3064 Hose or pipe clamps
Brand Name	Superstrut
Type	Pipe Straps, Pipe Clamps & Hangers (Series 700)
Special Features	Bolt head is combination slot and hex head for flexibility of attachment
Application	Superstrut Pipe Straps are designed to be twist inserted anywhere along the slot side of the channel.
Material	Steel
Finish	GoldGalv/Standard
Maximum Clamp Diameter	2.375 Inches
Minimum Clamp Diameter	2.195 Inches

European Specifications (ETIM)

ETIM	EC002470 Mounting clamp for cable protection tubes
Material	Steel
Rotatable	N

Packaging

Outer Quantity	50
Outer Dimensions (inches)	11.75x9x5.25
Weight Uom	37.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com