

- PDF was successfully created - CLICK LINK TO DOWNLOAD =>http://www.satco.com/media/PDF/satco_product_7552.pdf



S8648

19A21/LED/40K/120-277V
 19 watt; A21 LED; 4000K; Medium base; 220' beam spread; 120-277 volts

Features

- A-Shaped replacement lamp
- 125W equivalent
- Approved for enclosed fixtures
- Damp location rated



S8648

Item Number	UPC	Voltage	Watts	Operating Frequency	Incandescent Equivalent	Lamp Shape	Base
S8648	045923086489	120-277	19	50/60Hz	125W	A21	Medium
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
E26	19A21/LED/40K/120-277V	Non-Dimmable	Frosted	5-9/16"	2-5/8"	2000	25000
Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	ENERGY STAR
4000	Cool White	80	220	-25C (-13F) to a maximum of +45C (+113F)	24/6	Box	ENERGY STAR
CEC Status	RoHS Compliant	UL Classification	Warranty				
Non-Compliant	Yes	cULus - Damp Location Rated	5 Year Limited - 10 hour use per day				



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

