

WAC LIGHTING

FLO G2

Ceiling and Wall Mount

Model & Size	Color Temp & CRI	Lumens	Finish
WS-224G2 24"	2700K 90	1260	WT White
WS-236G2 36"		2015	
WS-248G2 48"	3000K 90	2395	
		1255	
	3500K 90	1915	
		2390	
		1500	
		2285	
		2730	

Example: **WS-224G2-27-WT**

DESCRIPTION

Multiple high-powered LEDs illuminate the acrylic diffuser uniformly without socket shadows which are common in conventional acrylic diffusers. Flo G2 may be used as a flush mount, under cabinet light, or as bathroom vanity and wall sconce.

FEATURES

- Multiple LED array for uniform illumination
- Driver concealed within the fixture
- 5 year warranty

SPECIFICATIONS

Construction:	Aluminum with white acrylic diffuser
Power:	30W, 25W, 16W
Input:	120-277 VAC, 50/60Hz
Dimming:	TRIAC: 100-5%, ELV: 100-5%
Light Source:	Integrated LED
Lens:	Translucent acrylic diffuser
Rated Life:	50000 Hours
Mounting:	Installs over a 3" or 4" Junction Box, Can be mounted on ceiling or wall in all orientations
Finish:	Electrostatically Powder Coated White
Operating Temp:	-4°F to 104°F (-20°C to 40°C)
Standards:	ETL, cETL, Damp Location Listed, Energy Star 2.0, Title 24 JA8-2016 Compliant, ADA

REPLACEMENT PARTS

- RPL-SHA-248G2 - 48" Replacement Shade
- RPL-SHA-236G2 - 36" Replacement Shade
- RPL-SHA-224G2 - 24" Replacement Shade

Fixture Type: _____

Catalog Number: _____

Project: _____

Location: _____



FINISHES



White

LINE DRAWING

