



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Eaton Arrow Hart Color Coded Locking Plug

AHCL1420P

UPC:032664755682

### Dimensions:

- **Height:** 2.92 IN
- **Length:** 2.13 IN
- **Width:** 2.3 IN

**Weight:** .4 LB

### Warranties:

### Specifications:

- **Special Features:** Voltage Color Coding
- **Type:** Locking Plug
- **Allowable Wire Size:** #14-8 AWG
- **Amperage Rating:** 20A
- **Application:** Industrial
- **Voltage Rating:** 125/250V
- **Wiring Method:** Back
- **Color:** Orange, Black
- **Design Type:** Ultra grip
- **Face/Body Material:** Nylon
- **Nema Configuration:** L14-20
- **Number Of Poles:** Three-pole
- **Number Of Wires:** Four-wire
- **Cord Diameter:** 0.38 - 1.16" (9.5 - 29.5mm)
- **Operating Temperature:** -40°C (w/o impact) to 60°C (-40°F to 140°F)

### Supporting documents:

- [ah-color-coded-L14-20-locking-devices-spec-sheet.pdf](#)

### Certifications:

- cULus Listed
- NOM



**Product compliance:**

- RoHS Compliant
- NAFTA

---

© 2016 Eaton. All rights reserved.