



IPL4-3 SHOWN

PART NUMBER	NO. OF PORTS	LENGTH
IPL4-3	3	1.55
IPL4-4	4	1.97
IPL4-5	5	2.39
IPL4-6	6	2.81
IPL4-8	8	3.66

WIRE ENTRY PORT
WIRE RANGE: #4 - #14 AWG
PRE-FILLED W/ OXIDE INHIBITOR

CONTACT NSi FOR SALES @ 800.321.5847

NOTES:

- CONNECTOR MANUFACTURED FROM 6061-T6 ALUMINUM ALLOY.
- UL LISTED PER UL486A/B SPECIFICATIONS FOR 600V.
- DUAL RATED FOR 90°C COPPER AND/OR ALUMINUM CONDUCTOR.
- COLD TEMPERATURE RATED TO -45°C.
- HIGH DIELECTRIC STRENGTH INSULATION IS ABRASION, CHEMICAL AND UV RESISTANT.

		POLARIS SALES CO. INC					
<small>PROPRIETARY AND CONFIDENTIAL</small>		<small>11625 PROSPEROUS DRIVE ODESSA, FL 33556</small>					
<small>THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF POLARIS SALES CO. INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF POLARIS SALES CO. INC. IS PROHIBITED.</small>		TITLE: INSULATED #4 CONNECTOR					
<table border="1"> <tr> <td style="width: 50%;"><small>NAME</small></td> <td style="width: 50%;"><small>DATE</small></td> </tr> <tr> <td><small>L. HILL</small></td> <td><small>07/14/10</small></td> </tr> </table>		<small>NAME</small>	<small>DATE</small>	<small>L. HILL</small>	<small>07/14/10</small>	DWG. NO. IPL4-	
<small>NAME</small>	<small>DATE</small>						
<small>L. HILL</small>	<small>07/14/10</small>						
MATERIAL: N/A		SCALE: N/A	SHEET: 1 OF 1				