


Rectangular Floor Boxes

1-, 2- and 3-Gang Rectangular Floor Box

Carlton® Rectangular Floor Box Systems — three-way power, data and communications plus easy double- or triple-gang, too.

Compared to metal boxes, Carlton® rectangular floor boxes cost less and install faster to save you money on every job. Three-in-one power, data and communications capability cuts installation time and cost even more, while simple two- and three-gang modularity gives you the flexibility, installation ease and cost-savings no other non-metallic boxes can match. The covers attach without the use of fasteners, providing a professional, clean installation as well as preserving the aesthetic life of the product. Take a closer look at all that our rectangular floor box systems offer you.



Features:



- Covers require no adjusting collar — two screws ensure a flush, secure installation
- Non-metallic PVC construction, watertight gasket and corrosion-resistant hardware ensure long life and reliable performance, even in harsh and/or corrosive environments
- One consistent box depth simplifies ordering time and reduces inventory
- Saves time and money on installations with simple saw cut to floor level
- Concrete tight and suitable for any on-grade/ below-grade application; concrete or wood subfloor construction approved
- Convenient cubic inch capacity markings on inside enable easy inspection
- PVC-molded ports and reducer plugs included
- Accepts 1/2", 3/4" and 1" conduit, tubing or raceway
- Rectangular sides are drillable
- For tile and carpet applications
- Cover options include solid brass, stainless steel and non-metallic (brown, slate and caramel)
- UL® scrubwater tested, approved for all types of finish flooring

Rectangular Floor Boxes


Gangable Rectangular Floor Box

Installation:

With our rectangular boxes, one SKU is all you ever need. Simply remove appropriate sides and slide boxes together to create two- or three-gang boxes for on-the-job flexibility no competitor offers.



CAT. NO.	MATERIAL	SIZE	INTERNAL VOLUME (CU. IN.)	MIN. CONCRETE DEPTH	HUBS (IN.)	REDUCER PLUGS (IN.)	STD. CTN.	STD. WT. (LBS.)
E976RFB	PVC	1-Gang	97.4 (16.8 per inch of depth)	3½	(2) 1	(2) 1 x ¾ (2) ¾ x ½	3	6.92



Activation Kit

Activation kit provides components to accommodate all standard power, data and communications devices, plus a divider to separate power from data and communications — all in a single SKU. Device yokes can be adjusted to store excess cord in the box.

CAT. NO.	MATERIAL	STD. CTN.	STD. WT. (LBS.)
E976AK2	PVC	3	2.47



Rectangular Floor Boxes



1-, 2- and 3-Gang Non-Metallic Floor Box Covers

On-the-job flexibility extends to our rectangular box covers. Each one-, two- or three-gang cover is suitable for any wiring application and can be used with any floor surface. Non-metallic covers are even field-reversible for tile or carpet. Double-door feature enables easy access to the device and helps keep stray cords organized.

Carlton® Rectangular Floor Box Covers do not require a separate carpet flange. The carpet flange is part of the cover and may be removed for tile application.

Features:

- High-impact resistant thermoplastic
- Field reversible for tile or carpet
- Gasketed for a watertight seal
- Double-door design
- For tile and carpet applications
- UL scrubwater tested





CAT. NO.	SIZE	COLOR	CARPET FLANGE	DIMENSIONS (W X L) (IN.)	STD. CTN.	STD. WT. (LBS.)
E9761B	One-Gang	Brown	Included	7.13 x 5.00	3	1.7
E9762B	Two-Gang	Brown	Included	7.13 x 8.25	9	8.5
E9763B	Three-Gang	Brown	Included	7.13 x 11.50	6	7.5
E9761C	One-Gang	Caramel	Included	7.13 x 5.00	3	1.7
E9762C	Two-Gang	Caramel	Included	7.13 x 8.25	9	8.5
E9763C	Three-Gang	Caramel	Included	7.13 x 11.50	6	7.5
E9761S	One-Gang	Slate	Included	7.13 x 5.00	3	1.7
E9762S	Two-Gang	Slate	Included	7.13 x 8.25	9	8.5
E9763S	Three-Gang	Slate	Included	7.13 x 11.50	6	7.5

1-, 2- and 3-Gang Solid Brass and Stainless Steel Floor Box Covers




Carlton® Brass and Stainless Steel Rectangular Floor Box Covers add a classic touch to all floor box installations, and are particularly suited for use in high-traffic areas because of the resistance to wear. The gasket gives a watertight seal, and the light lacquer finish provides extra protection.

Features:

- Rugged construction
- Coated with a light lacquer finish for extra protection
- Covers include a cord door
- Gasketed for watertight applications
- Accepts single, duplex, GFCI and low-voltage receptacles
- For tile and carpet applications
- UL scrubwater tested



One-Gang



Two-Gang

Three-Gang



CAT. NO.	SIZE	COLOR	STD. CTN.	STD. WT. (LBS.)
E9761BR	One-Gang	Brass	3	6.8
E9762BR	Two-Gang	Brass	3	9.9
E9763BR	Three-Gang	Brass	3	12.1
E9761SS	One-Gang	Stainless Steel	3	7.4
E9762SS	Two-Gang	Stainless Steel	3	11.6
E9763SS	Three-Gang	Stainless Steel	3	17.2
Rectangular Floor Box Activation Kit				
E976AK2	—	—	3	1.3