

GE Disconnect Quick Selection Guide

General & Heavy Duty Disconnects (240V & 600V) through 600A

| Duty | Volts | Fusible or Non-Fusible | Poles | Amperage | Indoor Type 1 Enclosure | Outdoor Type 3R Enclosure | Indoor / Outdoor Neutral | Stainless Steel Type 4X Enclosure | Stainless Steel Neutral | | | |
|---------|-------|------------------------|-------------|----------|-------------------------|-----------------------------|--------------------------|-----------------------------------|-------------------------|----------|----------|--|
| General | 240V | Fusible | 2 | 30 | TG3221 | TG3221R | Included | See Heavy Duty for Type N4X | | | | |
| | | | | 60 | TG3222 | TG3222R | | | | | | |
| | | | | 100 | TG3223 | TG3223R | | | | | | |
| | | | | 200 | TG3224 | TG3224R | | | | | | |
| | | | | 400 | TG3225 | TG3225R | | | | | | |
| | | | | 600 | TG3226 | TG3226R | | | | | | |
| | | | 3 | 30 | TG4321 | TG4321R | | | | | | |
| | | | | 60 | TG4322 | TG4322R | | | | | | |
| | | | | 100 | TG4323 | TG4323R | | | | | | |
| | | | | 200 | TG4324 | TG4324R | | | | | | |
| | | | | 400 | TG4325 | TG3325R ¹ | | | | | | |
| | | | | 600 | TG4326 | TG3326R ¹ | | | | | | |
| | | Non-Fusible | 3 | 30 | TGN3321 | TGN3321R | TNI21 | | | | | |
| | | | | 60 | TGN3322 ³ | TGN3322R ³ | | | | | | |
| | | | | 100 | TGN3323 ³ | TGN3323R ³ | | | | | | |
| | | | | 200 | TGN3324 | TGN3324R | TNIA64 | | | | | |
| | | | | 400 | TGN3325 | See Heavy Duty Type For N3R | TNI65 | | | | | |
| | | | | 600 | TGN3326 | See Heavy Duty Type For N3R | TNI66 | | | | | |
| Heavy | 240V | Fusible | 2 | 30 | TH3221 | TH3221R | Included | Included | | | | |
| | | | | 60 | TH3222 | TH3222R | | | | | | |
| | | | | 100 | TH3223 | TH3223R | | | | | | |
| | | | | 200 | TH3224 | TH3224R | | | | | | |
| | | | | 400 | TH3225 | TH3225R | | | | | | |
| | | | | 600 | TH3226 | TH3226R | | | | | | |
| | | | 3 | 30 | TH4321 | TH4321R | | | | Included | Included | |
| | | | | 60 | TH4322 | TH4322R | | | | | | |
| | | | | 100 | TH4323 | TH4323R | | | | | | |
| | | | | 200 | TH4324 | TH4324R | | | | | | |
| | | | | 400 | TH4325 | TH3325R ¹ | | | | | | |
| | | | | 600 | TH4326 | TH3326R ¹ | | | | | | |
| | 600V | Fusible | 3 | 30 | TH3361 | TH3361R | TNI62 | TH3361SS | TNIJ61 | | | |
| | | | | 60 | TH3362 | TH3362R | TNIA62 | TH3362SS | TNIJ62 | | | |
| | | | | 100 | TH3363 | TH3363R | TNIA63 | TH3363SS | TNIJ63 | | | |
| | | | | 200 | TH3364 | TH3364R | TNIA64 | TH3364SS | TNIJ64 | | | |
| | | | | 400 | TH3365 | TH3365R | TNI65 | TH3365SS | TNIJ66 | | | |
| | | | | 600 | TH3366 | TH3366R | TNI66 | TH3366SS | TNIJ66 | | | |
| | | | Non-Fusible | 3 | 30 | THN3321 ² | | TNI21 | | | | |
| | | | | | 30 | THN3361 | THN3361R | TNI62 | THN3361SS | TNIJ61 | | |
| | | | | | 60 | THN3362 | THN3362R | TNI62 | THN3362SS | TNIJ62 | | |
| | | | | | 100 | THN3363 | THN3363R | TNI63 | THN3363SS | TNIJ63 | | |
| | | | | | 200 | THN3364 | THN3364R | TNIA64 | THN3364SS | TNIJ64 | | |
| | | | | | 400 | THN3365 | THN3365R | TNI65 | THN3365SS | TNIJ66 | | |
| | | 600 | THN3366 | THN3366R | TNI66 | THN3366SS | TNIJ66 | | | | | |



Emergency Power Transfer Switches, Non-Fusible

| Amperage | Outdoor NEMA Type 3R | | |
|----------|-----------------------------|-------------------------|--------------------------|
| | 2 Pole / 3 Wire 120/240 Vac | 3 Pole / 3 Wire 240 Vac | Indoor / Outdoor Neutral |
| 100 | TC10323R | | Included |
| 200 | TC10324R | TC10424R | |



We have a full line of Double Throw Disconnects from 30A - 1200A . Enclosure options include NEMA 1 Indoor, NEMA 3R Outdoor and NEMA 4X Stainless Steel. Contact your GE sales rep for more information.

AC Pullout Disconnects (Steel N3R Outdoor Enclosure)

| Duty | N3R Outdoor Enclosure | Volts | Fusible or Non-Fusible | Poles | Amperage | Catalog No. |
|------------|-----------------------|----------|------------------------|-------|----------|-------------|
| AC Pullout | Steel | 240V | Non-Fusible | 2 | 60 | TFN60R |
| | | 120/240V | Fusible | | 60 | TF60R |
| | | 120/240V | Fusible | | 30 | TF30R |



AC Pullout Disconnects (Plastic N3R Outdoor Enclosure)

| Duty | N3R Outdoor Enclosure | Volts | Fusible or Non-Fusible | Poles | Amperage | Catalog No. |
|------------|-----------------------|----------|------------------------|-------|----------|-------------|
| AC Pullout | Plastic | 240V | Non-Fusible | 2 | 60 | TPN60R1 |
| | | 120/240V | Fusible | | 60 | TPF60R |
| | | 120/240V | Fusible | | 30 | TPF30R |



Disconnect Ground Kits

| Duty | Disconnect Enclosure Type | Volts | Fusible or Non-Fusible | Amperage | Ground Kit Catalog No. |
|-----------------------|---------------------------|--------------|------------------------|----------|------------------------|
| General or Heavy Duty | Any | 240V or 600V | Fusible or Non-Fusible | 30 | TGL1 |
| | | | | 60 | TGL1 |
| | | | | 100 | TNG3 |
| | | | | 200 | TNG3 |
| | | | | 400 | TGL6 |
| | | | | 600 | TGL6 |



This counter mat displays a portion of GE's disconnect offering. We offer a full line of 30A - 1200A disconnects and accessories. See publication **DET-845 Spec Setter* Safety Switches** or contact your GE sales rep for more information.

¹ Neutral not included. Order TNI65 or TNI66 separately.
² 240V max.
³ A neutral is not available. If one is required use Heavy Duty version.