









## Midway

### Midway Size Nylon Wallplates

DESCRIPTION	COLOR	CAT. NO.	IND. NO.
<b>1-GANG</b> <b>1-Blank Box Mount</b> 	IVORY	PJ13-I	—
	BLACK	PJ13-E	—
	GRAY	PJ13-GY	—
	RED	PJ13-R	—
	WHITE	PJ13-W	—
	BROWN	PJ13	—
ALMOND	PJ13-A	—	
<b>2-GANG</b> <b>2-Blank Box Mount</b> 	IVORY	PJ23-I	—
	BLACK	PJ23-E	—
	GRAY	PJ23-GY	—
	WHITE	PJ23-W	—
	ALMOND	PJ23-A	—
<b>1-GANG</b> <b>1-Telephone .406" dia. Hole, Box Mount</b> 	IVORY	PJ11-I	—
	BLACK	PJ11-E	—
	GRAY	PJ11-GY	—
	WHITE	PJ11-W	—
	ALMOND	PJ11-A	—
<b>2-GANG</b> <b>1-Toggle, 1-Duplex</b> 	IVORY	PJ18-I	—
	BLACK	PJ18-E	—
	GRAY	PJ18-GY	—
	WHITE	PJ18-W	—
	ALMOND	PJ18-A	—
<b>2-GANG</b> <b>1-Toggle 1-Decora</b> 	IVORY	PJ126-I	—
	WHITE	PJ126-W	—
	BROWN	PJ126	—
	ALMOND	PJ126-A	—
<b>3-GANG</b> <b>2-Toggle 1-Decora</b> 	IVORY	PJ226-I	—
	WHITE	PJ226-W	—
	BROWN	PJ226	—
	ALMOND	PJ226-A	—
<b>2-GANG</b> <b>1-Decora 1-Duplex</b> 	IVORY	PJ826-I	SPJ826-I
	WHITE	PJ826-W	SPJ826-W
	BROWN	PJ826	—
	ALMOND	PJ826-A	—

### Midway Size Nylon Wallplates — Power Receptacle


<b>1-GANG</b> <b>2.465" dia. Hole, Power Receptacle</b> <b>30 &amp; 50 Amp</b> 	IVORY	80532-I	—
	WHITE	80532-W	—
	BLACK	80532-E	—

See page G26 for Engraved Metal Wallplates.  
All devices are UL Listed and CSA Certified.


### Midway Wallplates

All Leviton Midway wallplates can be mounted onto larger volume outlet boxes and/or used to hide wall irregularities. All 1-Gang Midway wallplates are 4.875" H x 3.125" W. Midway wallplates are a full 0.375" higher and wider than standard wallplates.

#### Standard Size



#### Midway Size



For more information regarding matching wallplates, colors, materials, single and multi-gang, refer to Decora Devices, Section A, and Decora Home Controls, Section B.