



Shown actual size: non-insert style seeTouch 5-button keypad with raise/lower in White (QSWS2-5BRLN-WH)

### Features and capacities

- Available with 1–7 buttons in insert and non-insert styles
- Large rounded buttons are easy to use
- Each keypad includes two contact closures
- Coordinating Architectural or Claro® wallplates may be included depending on finish, see pg. 366 for further information
- Multi-gang wallplates available; up to 6-gang, see pg. 368
- For information on engraving, text symbols and backlit buttons/backlit text, see pg. 376
- A QS system can have up to 100 devices such as GRAFIK Eye® control units, keypads or shades
- Backlit buttons with engraving make it easy to find and operate wallstation in low light conditions

### Shade control

- Models available with group control settings for a single shade or multiple shades

### Dimensions and mounting

- Width: 2.75 in (70 mm); Height: 4.56 in (116 mm); Depth: 1.40 in (36 mm); Profile: .31 in (8 mm)
- Mounts in a standard 1-gang U.S. backbox

### Communication and wiring

- Operates via low-voltage IEC PELV/NEC Class 2 standard wired communication on the QS link
- Uses one power draw unit on the QS link

[Download this catalog section](#)


[Download specification submittal](#)

[Download high resolution product image](#)

[Download engraving sheet for Architectural finishes](#)

[Download engraving sheet for Satin Color finishes](#)

## Available finishes



Use **BOLD** color code in model number (Example: QSW2-2BN-**SW**)

**Satin finishes** (Available for insert style keypads; coordinating **faceplates ordered separately**)

						
<b>SW</b> Snow <b>F, B</b> Gray <b>E</b>	<b>LS</b> Limestone <b>F</b> Gray <b>B</b> White <b>E</b>	<b>BI</b> Biscuit <b>F, B</b> Gray <b>E</b>	<b>ES</b> Eggshell <b>F, B</b> Gray <b>E</b>	<b>PD</b> Palladium <b>F</b> Gray <b>B</b>	<b>TP</b> Taupe <b>F, B</b> Gray <b>E</b>	<b>ST</b> Stone <b>F</b> Gray <b>B</b> White <b>E</b>
						
<b>BG</b> Bluestone <b>F</b> Gray <b>B</b> White <b>E</b>	<b>PL</b> Plum <b>F</b> Taupe <b>B</b> Gray <b>E</b>	<b>SG</b> Sea Glass <b>F</b> Gray <b>B</b> White <b>E</b>	<b>TQ</b> Turquoise <b>F</b> Gray <b>B</b> White <b>E</b>	<b>GS</b> Goldstone <b>F</b> Ivory <b>B</b> Gray <b>E</b>	<b>DS</b> Desert Stone <b>F</b> Taupe <b>B</b> Gray <b>E</b>	<b>GB</b> Greenbriar <b>F</b> Gray <b>B</b> White <b>E</b>
						
<b>MS</b> Mocha Stone <b>F</b> Taupe <b>B</b> Gray <b>E</b>	<b>TC</b> Terracotta <b>F</b> Taupe <b>B</b> Gray <b>E</b>	<b>SI</b> Sienna <b>F</b> Brown <b>B</b> White <b>E</b>	<b>HT</b> Hot <b>F</b> Taupe <b>B</b> Gray <b>E</b>	<b>MR</b> Merlot <b>F</b> Taupe <b>B</b> Gray <b>E</b>	<b>MN</b> Midnight <b>F, B</b> Gray <b>E</b>	

Bold color code indicates faceplate color. Models include button kit in coordinating colors as shown.

Text engraving color varies by button color. Lighter colored buttons use gray text and darker colored buttons use white text. Visit [www.lutron.com/engraving](http://www.lutron.com/engraving) for further information.

**Architectural matte finishes** (Available for insert and non-insert style keypads; coordinating faceplates included)



**WH**  
White F, B  
Gray E



**LA**  
Light Almond F, B  
Gray E




**AL**  
Almond F, B  
Gray E



**BE**  
Beige F, B  
Gray E



**IV**  
Ivory F, B  
Gray E



**TP**  
Taupe F, B  
(non-insert only)  
Gray E



**GR**  
Gray F, B  
White E



**BR**  
Brown F, B  
White E



**BL**  
Black F, B  
White E

**Architectural metal finishes** (Available for insert and non-insert style keypads; coordinating faceplates included)



**BN**  
Bright Nickel F  
Black B  
White E



**BC**  
Bright Chrome F  
Black B  
White E



**CLA**  
Clear Anodized Aluminum F  
Black B  
White E



**SC**  
Satin Chrome F  
Black B  
White E



**SN**  
Satin Nickel F  
Black B  
White E



**QZ**  
Antique Bronze F  
Black B  
White E



**BB**  
Bright Brass F  
Black B  
White E



**BRA**  
Brass Anodized Aluminum F  
Black B  
White E



**SB**  
Satin Brass F  
Black B  
White E




**QB**  
Antique Brass F  
Black B  
White E



**BLA**  
Black Anodized Aluminum F  
Black B  
White E

## Explanation of features



seeTouch QS keypad  
insert and non-insert styles

.31 in 1.09 in  
(8 mm) (28 mm)




### Features

<p><b>1</b> Scene buttons</p>	<ul style="list-style-type: none"> <li>• Available with 1–7 scene preset options</li> <li>• Models available to provide zone, partition and shade control</li> </ul>
<p><b>2</b> Status LEDs</p>	<ul style="list-style-type: none"> <li>• Show which keypad button has been activated</li> </ul>
<p><b>3</b> Backlit buttons</p>	<ul style="list-style-type: none"> <li>• Easy to read and use in low-light conditions</li> </ul>
<p><b>4</b> Infrared (IR) receiver (optional)*</p>	<ul style="list-style-type: none"> <li>• Offers convenient control of lights/shades from an IR remote control, see pg. 197</li> </ul>
<p><b>5</b> Raise/lower buttons</p>	<ul style="list-style-type: none"> <li>• Brightens/dims all lighting or raises/lowers all assigned shades</li> </ul>
<p><b>6</b> Insert (top) and non-insert styles (bottom)</p>	<ul style="list-style-type: none"> <li>• Insert style wallstations use standard decora style wallplates for single and multi-gang configurations</li> <li>• Non-insert style wallstations feature simplified wallplate design</li> </ul>
<p><b>7</b> Dual button configurations</p>	<ul style="list-style-type: none"> <li>• Wallstation functions as two independently programmable controllers; each dual wallstation can control lighting zones, shade groups, or a combination of both simultaneously</li> </ul>


\* GRX-IT or GRX-8IT recommended

## Available models


(Available in insert and non-insert styles, non-insert style shown)




1, 2, 3, 5, 7-button



2, 3, 5-button with raise/lower  
(model numbers on following page)



2, 3, 5-button with IR and raise/lower  
(model numbers on following page)



Dual configurations  
(model numbers on following page)

## Model numbers

### Keypads

#### 1-button

Non-insert style	QSW2-1BN- <b>AA</b> <sup>1</sup> - <b>CCC</b>
Insert style	QSW2-1BI- <b>AA</b> <sup>4</sup> - <b>CCC</b>

#### 2-button

Non-insert style	QSW2-2BN- <b>AA</b> <sup>1</sup> - <b>CCC</b>
Insert style	QSW2-2BI- <b>AA</b> <sup>4</sup> - <b>CCC</b>

#### 3-button

Non-insert style	QSW2-3BN- <b>AA</b> <sup>1</sup> - <b>CCC</b>
Insert style	QSW2-3BI- <b>AA</b> <sup>4</sup> - <b>CCC</b>

#### 5-button

Non-insert style	QSW2-5BN- <b>AA</b> <sup>1</sup> - <b>CCC</b>
Insert style	QSW2-5BI- <b>AA</b> <sup>4</sup> - <b>CCC</b>

#### 7-button

Non-insert style	QSW2-7BN- <b>AA</b> <sup>1</sup> - <b>CCC</b>
Insert style	QSW2-7BI- <b>AA</b> <sup>4</sup> - <b>CCC</b>

Compatible with GRAFIK Eye® QS, GRAFIK Eye QS with EcoSystem®, all Energi Savr Node™ systems and Lutron® guestroom solutions.

**AA**<sup>1</sup>: Architectural matte and metal color codes, see pg. 205

**AA**<sup>4</sup>: Architectural matte, metal and Satin color codes, see pg. 204–205  
(Coordinating wallplates not included with Satin colors, order separately, see pg. 366)

**CCC**: Engraving codes, see pg. 376

## Model numbers

### Keypads with raise/lower

#### 2-button with raise/lower

Non-insert style	QSW2-2BRLN- <b>AA</b> <sup>1</sup> - <b>CCC</b>
Insert style	QSW2-2BRLI- <b>AA</b> <sup>4</sup> - <b>CCC</b>

#### 3-button with raise/lower

Non-insert style	QSW2-3BRLN- <b>AA</b> <sup>1</sup> - <b>CCC</b>
Insert style	QSW2-3BRLI- <b>AA</b> <sup>4</sup> - <b>CCC</b>

#### 5-button with raise/lower

Non-insert style	QSW2-5BRLN- <b>AA</b> <sup>1</sup> - <b>CCC</b>
Insert style	QSW2-5BRLI- <b>AA</b> <sup>4</sup> - <b>CCC</b>

Compatible with GRAFIK Eye® QS, GRAFIK Eye QS with EcoSystem®, all Energi Savr Node™ systems and Lutron® guestroom solutions.

### Keypads with IR and raise/lower

#### 2-button with IR and raise/lower

Non-insert style	QSW2-2BRLIRN- <b>AA</b> <sup>1</sup> - <b>CCC</b>
Insert style	QSW2-2BRLIRI- <b>AA</b> <sup>4</sup> - <b>CCC</b>

#### 3-button with IR and raise/lower

Non-insert style	QSW2-3BRLIRN- <b>AA</b> <sup>1</sup> - <b>CCC</b>
Insert style	QSW2-3BRLIRI- <b>AA</b> <sup>4</sup> - <b>CCC</b>

#### 5-button with IR and raise/lower

Non-insert style	QSW2-5BRLIRN- <b>AA</b> <sup>1</sup> - <b>CCC</b>
Insert style	QSW2-5BRLIRI- <b>AA</b> <sup>4</sup> - <b>CCC</b>

### Dual configuration keypads

#### Dual 2-button with raise/lower

Non-insert style	QSW2-2RLDN- <b>AA</b> <sup>1</sup> - <b>CCC</b>
Insert style	QSW2-2RLDI- <b>AA</b> <sup>4</sup> - <b>CCC</b>

#### Dual 3-button and 2-button with raise/lower

Non-insert style	QSW2-1RLDN- <b>AA</b> <sup>1</sup> - <b>CCC</b>
Insert style	QSW2-1RLDI- <b>AA</b> <sup>4</sup> - <b>CCC</b>

#### Dual 3-button

Non-insert style	QSW2-3BDN- <b>AA</b> <sup>1</sup> - <b>CCC</b>
Insert style	QSW2-3BDI- <b>AA</b> <sup>4</sup> - <b>CCC</b>

Compatible with GRAFIK Eye QS, GRAFIK Eye QS with EcoSystem, all Energi Savr Node systems and Lutron guestroom solutions.

**AA**<sup>1</sup>: Architectural matte and metal color codes, see pg. 205

**AA**<sup>4</sup>: Architectural matte, metal and Satin color codes, see pgs. 204–205

**CCC**: Engraving codes, see pg. 376  
(Faceplates ship with matte and metal finishes, but should be ordered separately for satin finish keypads)

Insert style keypads may ship with Architectural or Designer style faceplates depending on finish; Non-insert style keypads ship with Architectural faceplates.

## Model numbers

### Faceplate kits

#### 1-button

Non-insert style	QSW2R-1BN- <b>AA</b> <sup>1</sup> - <b>CCC</b>
Insert style	QSW2R-1BI- <b>AA</b> <sup>4</sup> - <b>CCC</b>

#### 2-button

Non-insert style	QSW2R-2BN- <b>AA</b> <sup>1</sup> - <b>CCC</b>
Insert style	QSW2R-2BI- <b>AA</b> <sup>4</sup> - <b>CCC</b>

#### 3-button

Non-insert style	QSW2R-3BN- <b>AA</b> <sup>1</sup> - <b>CCC</b>
Insert style	QSW2R-3BI- <b>AA</b> <sup>4</sup> - <b>CCC</b>

#### 5-button

Non-insert style	QSW2R-5BN- <b>AA</b> <sup>1</sup> - <b>CCC</b>
Insert style	QSW2R-5BI- <b>AA</b> <sup>4</sup> - <b>CCC</b>

#### 7-button

Non-insert style	QSW2R-7BN- <b>AA</b> <sup>1</sup> - <b>CCC</b>
Insert style	QSW2R-7BI- <b>AA</b> <sup>4</sup> - <b>CCC</b>

Includes faceplates, buttons and insert.

Compatible with all seeTouch QS keypads.

### Faceplate kits with raise/lower

#### 2-button with raise/lower

Non-insert style	QSW2R-2BRLN- <b>AA</b> <sup>1</sup> - <b>CCC</b>
Insert style	QSW2R-2BRLI- <b>AA</b> <sup>4</sup> - <b>CCC</b>

#### 3-button with raise/lower

Non-insert style	QSW2R-3BRLN- <b>AA</b> <sup>1</sup> - <b>CCC</b>
Insert style	QSW2R-3BRLI- <b>AA</b> <sup>4</sup> - <b>CCC</b>

#### 5-button with raise/lower

Non-insert style	QSW2R-5BRLN- <b>AA</b> <sup>1</sup> - <b>CCC</b>
Insert style	QSW2R-5BRLI- <b>AA</b> <sup>4</sup> - <b>CCC</b>

Includes faceplates, buttons and insert.

Compatible with all seeTouch QS keypads.

**AA**<sup>1</sup>: Architectural matte and metal color codes, see pg. 205

**AA**<sup>4</sup>: Architectural matte, metal and Satin color codes, see pgs. 204–205

**CCC**: Engraving codes, see pg. 376  
(Faceplates ship with matte and metal finishes, but should be ordered separately for satin finish keypads)

Insert style keypads may ship with Architectural or Designer style faceplates depending on finish; Non-insert style keypads ship with Architectural faceplates.

## Model numbers

### Button kits \*

#### 1-button

Non-insert style	QSW2B-1BN- <b>AA</b> <sup>5</sup> - <b>CCC</b>
Insert style	QSW2B-1BI- <b>AA</b> <sup>6</sup> - <b>CCC</b>

#### 2-button

Non-insert style	QSW2B-2BN- <b>AA</b> <sup>5</sup> - <b>CCC</b>
Insert style	QSW2B-2BI- <b>AA</b> <sup>6</sup> - <b>CCC</b>

#### 3-button

Non-insert style	QSW2B-3BN- <b>AA</b> <sup>5</sup> - <b>CCC</b>
Insert style	QSW2B-3BI- <b>AA</b> <sup>6</sup> - <b>CCC</b>

#### 5-button

Non-insert style	QSW2B-5BN- <b>AA</b> <sup>5</sup> - <b>CCC</b>
Insert style	QSW2B-5BI- <b>AA</b> <sup>6</sup> - <b>CCC</b>

#### 7-button

Non-insert style	QSW2B-7BN- <b>AA</b> <sup>5</sup> - <b>CCC</b>
Insert style	QSW2B-7BI- <b>AA</b> <sup>6</sup> - <b>CCC</b>

### Button kits with raise/lower \*

#### 2-button with raise/lower

Non-insert style	QSW2B-2BRLN- <b>AA</b> <sup>5</sup> - <b>CCC</b>
Insert style	QSW2B-2BRLI- <b>AA</b> <sup>6</sup> - <b>CCC</b>

#### 3-button with raise/lower

Non-insert style	QSW2B-3BRLN- <b>AA</b> <sup>5</sup> - <b>CCC</b>
Insert style	QSW2B-3BRLI- <b>AA</b> <sup>6</sup> - <b>CCC</b>

#### 5-button with raise/lower

Non-insert style	QSW2B-5BRLN- <b>AA</b> <sup>5</sup> - <b>CCC</b>
Insert style	QSW2B-5BRLI- <b>AA</b> <sup>6</sup> - <b>CCC</b>

Compatible with seeTouch QS keypads.

\* Faceplate kits ordered separately

### Button kits with IR and raise/lower \*

#### 2-button with IR and raise/lower

Non-insert style	QSW2B-2BRLIRN- <b>AA</b> <sup>5</sup> - <b>CCC</b>
Insert style	QSW2B-2BRLIRI- <b>AA</b> <sup>6</sup> - <b>CCC</b>

#### 3-button with IR and raise/lower

Non-insert style	QSW2B-3BRLIRN- <b>AA</b> <sup>5</sup> - <b>CCC</b>
Insert style	QSW2B-3BRLIRI- <b>AA</b> <sup>6</sup> - <b>CCC</b>

#### 5-button with IR and raise/lower

Non-insert style	QSW2B-5BRLIRN- <b>AA</b> <sup>5</sup> - <b>CCC</b>
Insert style	QSW2B-5BRLIRI- <b>AA</b> <sup>6</sup> - <b>CCC</b>

### Dual configuration button kits \*

#### Dual 3-button and 2-button with raise/lower

Non-insert style	QSW2B-1RLDN- <b>AA</b> <sup>5</sup> - <b>CCC</b>
Insert style	QSW2B-1RLDI- <b>AA</b> <sup>6</sup> - <b>CCC</b>

#### Dual 2-button with raise/lower

Non-insert style	QSW2B-2RLDN- <b>AA</b> <sup>5</sup> - <b>CCC</b>
Insert style	QSW2B-2RLDI- <b>AA</b> <sup>6</sup> - <b>CCC</b>

#### Dual 3-button

Non-insert style	QSW2B-3BDN- <b>AA</b> <sup>5</sup> - <b>CCC</b>
Insert style	QSW2B-3BDI- <b>AA</b> <sup>6</sup> - <b>CCC</b>

Compatible with seeTouch QS keypads.

**AA**<sup>5</sup>: Limited Architectural matte finishes, see pg. 205 for corresponding button colors

**AA**<sup>6</sup>: Limited Satin finishes, see pg. 204 for corresponding button colors

**CCC**: Engraving codes, see pg. 376