

GFCI Receptacles with Auto Grounding


15 and 20 Ampere, 125 Volts AC, 2 Pole, 3 Wire Grounding



GFRST15WNL


Features

- Patented AUTOGUARD® self test technology includes disconnecting power to the receptacle if critical components are damaged and GFCI protection is lost
- Internal back wiring clamp and guide for quick and secure termination
- Night light option includes light sensor controls for automatic ON and OFF, custom dual lens for optimum light output



Standard

Rating	Color	Standard	Night Light Two LED Night Lights	Alarm	Assembled in USA	Blank Face Available in 20A Only	Standard 3-Pack Three Devices per Pack
	Almond	GFRST15AL	GFRST15ALNL	GFRST15ALB	GFRST15ALU	—	—
	Black	GFRST15BK	GFRST15BKNL	GFRST15BKB	GFRST15BKU	—	—
	Brown	GFRST15	GFRST15NL	GFRST15B	GFRST15U	—	—
	Gray	GFRST15GY	GFRST15GYNL	GFRST15GYB	GFRST15GYU	—	—
	Ivory	GFRST15I	GFRST15INL	GFRST15IB	GFRST15IU	—	GFRST15I3
	Light Almond	GFRST15LA	GFRST15LANL	GFRST15LAB	GFRST15LAU	—	GFRST15LA3
	Red	GFRST15R	GFRST15RNL	GFRST15RB	GFRST15RU	—	—
	White	GFRST15W	GFRST15WNL	GFRST15WB	GFRST15WU	—	GFRST15W3
	Almond	GFRST20AL	GFRST20ALNL	GFRST20ALB	GFRST20ALU	GFBFST20AL	—
	Black	GFRST20BK	GFRST20BKNL	GFRST20BKB	GFRST20BKU	GFBFST20BK	—
	Brown	GFRST20	GFRST20NL	GFRST20B	GFRST20U	GFBFST20	—
	Gray	GFRST20GY	GFRST20GYNL	GFRST20GYB	GFRST20GYU	GFBFST20GY	—
	Ivory	GFRST20I	GFRST20INL	GFRST20IB	GFRST20IU	GFBFST20I	GFRST20I3
	Light Almond	GFRST20LA	GFRST20LANL	GFRST20LAB	GFRST20LAU	GFBFST20LA	GFRST20LA3
	Red	GFRST20R	GFRST20RNL	GFRST20RB	GFRST20RU	GFBFST20R	—
	White	GFRST20W	GFRST20WNL	GFRST20WB	GFRST20WU	GFBFST20W	GFRST20W3



Tamper-Resistant Weather Resistant

Rating	Color	Standard	Assembled in USA	Isolated Ground
	Almond	GFTWRST15AL	GFTWRST15ALU	GFTWRST15ALIG
	Black	GFTWRST15BK	GFTWRST15BKU	GFTWRST15BKIG
	Brown	GFTWRST15	GFTWRST15U	GFTWRST15IG
	Gray	GFTWRST15GY	GFTWRST15GYU	GFTWRST15GYIG
	Ivory	GFTWRST15I	GFTWRST15IU	GFTWRST15IIG
	Light Almond	GFTWRST15LA	GFTWRST15LAU	GFTWRST15LAIG
	Red	GFTWRST15R	GFTWRST15RU	GFTWRST15RIG
	White	GFTWRST15W	GFTWRST15WU	GFTWRST15WIG
	Almond	GFTWRST20AL	GFTWRST20ALU	GFTWRST20ALIG
	Black	GFTWRST20BK	GFTWRST20BKU	GFTWRST20BKIG
	Brown	GFTWRST20	GFTWRST20U	GFTWRST20IG
	Gray	GFTWRST20GY	GFTWRST20GYU	GFTWRST20GYIG
	Ivory	GFTWRST20I	GFTWRST20IU	GFTWRST20IIG
	Light Almond	GFTWRST20LA	GFTWRST20LAU	GFTWRST20LAIG
	Red	GFTWRST20R	GFTWRST20RU	GFTWRST20RIG
	White	GFTWRST20W	GFTWRST20WU	GFTWRST20WIG