

## PRODUCT INFORMATION

**Intended Use**

For use where accent or task lighting is needed. Ideal for cabinet lighting in kitchens, offices and bookcases.

**Construction**

Slim-profile design with on/off switch. Rugged powder-coated steel hous-

ing. Acrylic diffuser provides soft, widespread illumination with zip-lock design for easy maintenance and superior retention. Available in white or bronze finish.

Plug-in: No wiring required; fixture-to-outlet connector included with each fixture.

Direct wire: Top or back-side flush knockouts provided. Pre-installed, poke-home connectors eliminate the need for wire nuts.

13" connector cord with safety lock included with fixture for linking additional fixtures together.

**Listings**

UL Listed to U.S. and Canadian safety standards. ENERGY STAR® qualified.

# LINKABLE T5 FLUORESCENT



Example: UC5D 8 120 LP


## ORDERING INFORMATION

Series <sup>1</sup>	Number of lamps	Voltage <sup>2</sup>	Lamped <sup>3</sup>	Finish
UCSD	8 12", (1) 8W T5 lamp	120 120V electronic ballasts (standard)	LP Lamp included (standard)	(blank) White
	14 23", (2) 14W T5 lamps			BZ Bronze
	21 34", (3) 21W T5 lamps			

## ADDITIONAL INFORMATION

For additional product information, visit [www.lightahome.com](http://www.lightahome.com).

Drawings are for dimensional detail only and may not represent actual mechanical configuration. Dimensions are shown in inches (centimeters) unless otherwise noted.

**Notes**

- 1 Maximum quantity of cabinet fixtures that can be connected from a single power source cannot exceed 540W from the lamp wattage.
- 2 Use with non-dimmable switches only.
- 3 Includes T5 fluorescent lamp.

## PRODUCT INFORMATION

**Intended Use**

Splice box: Allows for quick and easy direct wiring. Features snap-on cover, pre-installed poke-home wire connectors and mounting hardware.

24" cord connector: Linkable cabinet lights come standard with a 13" connector cord. A 24" connector cord is avail-

able for longer-length connections between fixtures.

Row connector: Row connectors allow continuous connections with minimal (1/8") spacing between fixtures. Side-by-side connections reduce shadow between fixtures for uninterrupted light across countertops or work areas.

Cord cover: 18" white cord cover keeps fixture-to-fixture connector cords and cord-and-plugs hidden.

Self-adhesive strip on upper side of cover adheres to most surfaces. Cord cover can be cut to accommodate shorter distances between fixtures.

# LINKABLE ACCESSORIES



## ORDERING INFORMATION

## ACCESSORIES/REPLACEMENT PARTS

UCD JB M12	Splice box for quick and easy direct wiring
UC ERC R12	1-1/8" row connector for end-to-end connections <sup>1</sup>
UC ERC24 R12	24" connector cord for longer-length connections <sup>1</sup>
UCH WWC R12	18" white cord cover for concealing cord <sup>1</sup>

## ADDITIONAL INFORMATION

For additional product information, visit [www.lightahome.com](http://www.lightahome.com).

**Notes**

- 1 Resale packs must be ordered in increments of 12.