


MOUNTING PADS



MOUNTING PADS

- Patented 'Stay-N-Place' feature is unique to ACT's mounting pads. This feature keeps cable ties from sliding down during vertical applications and maintains the placement of the cable ties during other installations.
- Patented 'Lead-N-Feature' allows for easy insertion of cable ties during awkward applications.
- Smooth radius cradle is designed to eliminate possible damage to cables while providing stable support.
- Webbed punch through screw hole allows maximum adhesive surface area with easy insertion of mechanical fastener. Screw hole is countersunk to allow ease of cable tie insertion.
- 4-sided entry slots save time during placement orientation.
- Low profile is essential when space is critical in confined areas.

ACT Part Number	Color & Material	Lgth/Wdth Inch/mm	Thickness Inch/mm	Slot Height Inch/mm	Slot Width Inch/mm	Screw Size	Adhesive	RU-CSA	Per Bag	Per Case
AL-MP-750-9-C	Natural Nylon	.74/18.79	.19/4.82	.05/1.27	.20/5.08	#4	Rubber	RU-CSA	100	1,000
AL-MP-750-0-C	Black Nylon									
AL-MP-1000-9-C	Natural Nylon	.99/25.14	.20/5.08	.06/1.52	.20/5.08	#6	Rubber	RU-CSA	100	1,000
AL-MP-1000-0-C	Black Nylon									
AL-MPA-750-9-C	Natural Nylon	.74/18.79	.19/4.82	.05/1.27	.20/5.08	#4	Acrylic	RU-CSA	100	1,000
AL-MPA-750-0-C	Black Nylon									
AL-MPA-1000-9-C	Natural Nylon	.99/25.14	.20/5.08	.06/1.52	.20/5.08	#6	Acrylic	RU-CSA	100	1,000
AL-MPA-1000-0-C	Black Nylon									
AL-MP-750-NT-9-C	Natural Nylon	.74/18.79	.19/4.82	.05/1.27	.20/5.08	#4	None	RU-CSA	100	1,000
AL-MP-750-NT-0-C	Black Nylon									
AL-MP-1000-NT-9-C	Natural Nylon	.99/25.14	.20/5.08	.06/1.52	.20/5.08	#6	None	RU-CSA	100	1,000
AL-MP-1000-NT-0-C	Black Nylon									

Mechanical Strength: 0.75" = 9 lbs/40n., 1.0" = 11 lbs/50n. Sold in case quantities. Also available in 5000 per case quantities.

Related product lines



Standard Cable Ties



Releasable Cable Ties



Double Head Cable Ties

ACT
 ADVANCED CABLE TIES, INC.
 245 Suffolk Lane, Gardner, MA 01440
 Phone: 800.861.7228 - Fax: 978.630.3999
 sales@actfs.com

