


















Emergency, Oil & Gas Burner

OIL BURNER	DESCRIPTION	CAT. NO.	GAS BURNER	DESCRIPTION	CAT. NO.
	4 Inch Square Oil Burner Cover (Red with white ltrs.) 1/2" Raised (1920)	41009		4 Inch Square Gas Burner Cover (Red with white ltrs.) 1/2" Raised (192G)	41026
	3.25 Inch Round Oil Burner Cover (Red with white ltrs.) (30C)	41011		3.25 Inch Round Gas Burner Cover (Red with white ltrs.) (3GC)	41027
	4 Inch Round Oil Burner Cover (Red with white ltrs.) (40C)	41012		4 Inch Round Gas Burner Cover (Red with white ltrs.) (4GC)	41028

NEW ITEMS

OPENING, TEXT	MATERIAL, LETTERING	RED PAINTED STEEL	RED LEXAN®	TYPE 302 .035 SS Painted Red	OPENING, TEXT	MATERIAL, LETTERING	RED PAINTED STEEL	RED LEXAN®	TYPE 302 .035 SS Painted Red
		White 1/4" Silk Screening	White 1/4" Silk Screening	White Fill 1/4" Engraving			White 1/4" Silk Screening	White 1/4" Silk Screening	White Fill 1/4" Engraving
 Switch Box (Flush Mntg.) Toggle Switch "Emergency Switch/On-Off"		41052			 Switch Box (Flush Mntg.) 2 Duplex Receptacles "Emergency"		41058	42102	41242
 Utility/Handy Box Toggle Switch "Emergency/On-Off"		41055			 Switch Box (Flush Mntg.) Single Receptacle "Emergency"		41059	42091	41245
 Switch Box (Flush Mntg.) Toggle Switch "Emergency"			42071	41241	 Switch Box (Flush Mntg.) Block/Decorator Receptacle "Emergency"			42035	41244
 Switch Box (Flush Mntg.) 2 Toggle Switches "Emergency"		41056	42072	41243	 Switch Box (Flush Mntg.) 2 Block/Decorator Receptacles "Emergency"			42036	
 Switch Box (Flush Mntg.) 3 Toggle Switches "Emergency"			42073		 Switch Box (Flush Mntg.) Toggle/Duplex Receptacle "Emergency"			42032	
 Switch Box (Flush Mntg.) Duplex Receptacle "Emergency"		41057	42101	41240	SWITCH GUARD Prevent Accidents Cat. No. 40480 .030" Stainless Series 300 Spec. Grade-Non Magnetic (Plate not included)				