



Hazardous Location Fittings-PVC Coated
T&B Catalog Number:

UPC Number: UNY305-G
Status: 70450841395
Description: Active



PVC Coated Explosion and Dust-Ignition Proof UNY Male Union, Pipe Size 1 Inch/27 Metric, 3 Piece, for Hazardous and Non-hazardous Locations, Overall Length 2.75 Inch/69.85 Millimeters, Overall Diameter 2.00 Inch/50.80 Millimeters, ElectroGalvanized Steel, Gray

Features

Coated with a nominal .002 in. (2 mil) blue urethane on the interior, before PVC Coating is applied.
 A minimum .040 in. (40 mil) PVC Coating is bonded to the exterior.
 Pressure sealing sleeves to protect the connection.

Application

To connect conduit to a conduit fitting, junction box, or device enclosure.

General

Custom_Finish	uny_1
Trade Size (inches)	1
Material	Steel
Finish	PVC Coated
Color	Dark Gray

Dimension Information

Overall Length (inches)	2 3/4
Overall Diameter (inches)	2

Technical Information

Chemical Resistance Chart	Available on Website
---------------------------	----------------------

Specifications

Ocal Specification Guide-1995 Master Format-PDF	Available on Website
Ocal Specification Guide-1995 Master Format-DOC	Available on Website
Ocal Specification Guide-2004 Master Format-PDF	Available on Website
Ocal Specification Guide-2004 Master Format-DOC	Available on Website

Packaging

Package in Units	40
T&B Sold in UOM	Each
T&B Weight Per UOM	0.99 lbs. Each

Application Support

Ocal Specifications	Available on Website
Recommended Installation Procedures	Available on Website

Product Overview-Conduit Outlet Bodies	Available on Website
NEMA Standards-RN 1	Available on Website
NEC 310-16 - Conductors for General Wiring	Available on Website
NEC Table 8	Available on Website

Notes

Dimensional values are of uncoated fittings.
 Standard color is dark gray. Also available in white and light blue. Custom colors are also available upon request. Please contact Technical Services, 888-862-3289.

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com