

# GFTR1-HGW

# Tamper Resistant Receptacles

## Item Description

15 Amp, 125 Volt, SmartlockPro Slim Self-Test GFCI Receptacle, Extra-Heavy Duty Hospital Grade, Tamper-Resistant, NEMA 5-15R, 20A Feed-Through, 2P, 3W, Matching Wallplate Included - WHITE



## Technical Information

### AC Horsepower Ratings

**At Rated Voltage:** 1 HP

### Electrical Specifications

**Grounding:** Self-Grounding Clip

**Pole:** 2

**Wire:** 3

**Short Circuit Current Rating:** 10kA

### Environmental Specifications

**Flammability:** Rated V-0 per UL94

**Operating Temperature:** -35C to +66C

### Material Specifications

**Face Material:** PBT

**Body Material:** Polycarbonate

**Terminal Screws:** Plated Steel

**Terminal Clamp:** Brass

**Line Contacts:** Brass

**Grounding Screw:** Plated Steel

**Strap Material:** Galvanized Steel

**Ground Clips:** Brass

**Shutter Mechanism:** Delrin® Acetal

### Mechanical Specifications

**Terminal ID:** Brass-Hot, Green-Ground, Silver-Neutral

**Terminal Accom.:** 14-10 AWG solid or stranded

**Product ID:** Ratings are permanently marked on device

### Product Features

**Color:** White

**NEMA:** 5-15R

### Standards and Certifications

**NEMA:** WD-1 & WD-6

**ANSI:** C-73

**Certification/Listing:** UL, CSA, NOM-ANCE

**Applicable Standards:** UL 943, UL 498, CSA C22.2 No. 42 & 144, FedSpec W-C-596

### Warranty

**Product Warranty:** 2-Year Limited

**Color:**





White

**UPC Code:** 07847772361

**Country of Origin:** China

**NEMA:** 5-15R





SPECIFICATION SUBMITTAL

JOB NAME:	CATALOG NUMBERS:	
<input type="text"/>	<input type="text"/>	<input type="text"/>
JOB NUMBER:	<input type="text"/>	<input type="text"/>

**Leviton Manufacturing Co., Inc.**

201 North Service Road, Melville, NY 11747

Telephone: 1-800-323-8920 · FAX: 1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): 1-800-824-3005

**Leviton Manufacturing of Canada, Ltd.**

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: 1-800-469-7890 ·

FAX: 1-800-824-3005 · [www.leviton.com/canada](http://www.leviton.com/canada)

**Leviton S. de R.L. de C.V.**

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-1797 · [www.leviton.com.mx](http://www.leviton.com.mx)

**Visit our Website at: [www.leviton.com](http://www.leviton.com)**

© 2012-2016 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.

**Leviton has a global presence.**

If you would like to know where your local Leviton office is located please go to: [www.leviton.com/international/contacts/](http://www.leviton.com/international/contacts/)

