

# KSL SERIES - Universal Industrial T5 or T8

## Low Profile Strip Kit

reflect-a-light®

Made in USA
  Adjustable Bracket
  Universal Lamps
  Low Ceilings

### Application

- Warehouses
- Aisles
- Retail

### Benefits

- Instant On - Re-Strike
- Up To 90% Energy Savings
- EPACT and Utility Rebates

### Features

- Toolless Ballast Access
- BAA Qualified
- ETL Certified

### Photometry

- 2 Lamp 4' T8-KSL-02B04-SA
- Efficiency: 92.1%
- 0-DEG: 1.2
- 90-DEG: 1.7
- Report Number: 1389

### Design


- Made in USA
- Reflector Dimensions: 48.00" x 8.50" x 0.50"
- Quarter turn reflector design
- Reflectors produced on high speed roll form for consistent high quality
- Adjustable channel width bracket for 4" or 5" kits
- One-piece adjustable center bracket for 1 or 2 lamps
- Sockets snap-in & twist lock
- ETL Certified

### 4' Components

- (1) RSL
- (2) BSA
- (4) SO-FL205
- (4) QT
- (5) TK

### 8' Components

- (2) RSL
- (2) BSA
- (1) CSA
- (8) SO-FL-205
- (8) QT
- (9) TK



shown above:  
Reflector 1 Brackets 2 4' Components

Existing Fixture	Input Watts	System Lumens
4 Lamp F40 T12	192	9120
2 Lamp F40 T12	96	4560
4 Lamp F34 T12	144	7930
4 Lamp F34 T12	72	3960
Retrofit Options	Input Watts	System Lumens
2 Lamp F32 T8 Normal	57	5192
2 Lamp F32 T8 Low	51	4602
2 Lamp F32 T8 High	75	6961
2 Lamp F28 T8 HE/Normal	49	4654
2 Lamp F28 T8 HE/Low	43	4119
2 Lamp F28 T8 HE/High	66	6152

\*Lamp/ballast information provided from GE based on Proline ballast and F32T8/SPX41/ECO lamps.  
High efficient system based on GE Ultra Max ballast and F28T8/SPX41/ECO lamps

### Fixture Ordering Guide Example

KSL-UB04-WA-FLS

Series	Lamps	Wattage	Length	Material	Sockets
KSL	U - Universal	B - T8 C - T5	02 - 2'	EA - 95% Enhanced Aluminum SA - 86% Specular Aluminum WA - 91% White Aluminum	FLS - Shunted FLN - Non Shunted
			03 - 3'		
			04 - 4'		
			06 - 6'		
			08 - 8'		

NOTE: 4.25" to 5" is considered standard channel size. Wider Channel sizes are available and considered special order. Please contact a sales rep for information.

### Option Ordering Guide

See Standard Option Guide



Industry Leader in  
Customization + Lead Times  
for Over 25 Years

VIDALIA, GA  
1-800-537-1629

**US Energy Sciences**  
reflecting technology™