



Steel City[®]

Flush Service
T&B Catalog Number:

68 P
 78599160023
 Active

UPC Number:
Status:
Description:

Flush Service Floor Box, 100 Cubic Inches, Opening Diameter 5-5/32 Inches, Base Diameter 6-3/8 Inches, Depth 6 Inches, 3/4 Inch and 1 Inch Conduit Tapping, Plastic, For Power or Communications/Data

Features

High-strength rigid PVC construction, non-corrosive.

Easy installation with no leveling required, just cut the box level with the concrete after the pour.

Compatible with standard schedule PVC conduit.

Application

Provide flush service for power or communications and data.

Suitable for carpet, tile or wood applications.

General

Material	Non-Metallic
Volume (cu.in.)	100
Standard Conduit Tapping (inches)	(4)-3/4 & (2) - 1
After Pour Adjustment (inches)	None
Wiring Device	Single Duplex or Data/Voice
Box Material	Non-Metallic

Dimension Information

Dimension A (inches)	5 5/32
Dimension B (inches)	6
Dimension C (inches)	6 3/8

Specifications

3dmodel	Available on Website
Product Specification-DOC	Available on Website
Product Specification-PDF	Available on Website

Accessories & Components

68R Recessed Covers	sf_68rseries
Covers & Carpet Plates	sf_68p_acces

Competitor Cross Reference

Competitive Cross Reference Guide	Available on Website
-----------------------------------	----------------------

Packaging

T&B Inner Pack	1
Package in Units	8
T&B Sold in UOM	Each
T&B Weight Per UOM	1.88 lbs. Each

Application Support

T&B Sales Drawings	wsd-000393
--------------------	------------

T&B Instruction Sheets	ta01396-tb2ta03866-tb2
Product Overview	Available on Website
Product Brochure-68R Recessed Covers	Available on Website
Product Brochure-68P Dual Voltage Kits	Available on Website
Product Brochure-6 Inch Extension for 68P Floor Box	Available on Website
Floor Box Selection Guide	Available on Website

Notes

*Note	Concrete cap, six hub plugs and 1", 3/4", and 1/2" reducers included.
**Note	Must use 68-PAR to attach cover plates to 68-P floor box.
***Note	Minimum pour 3 inches. Cubic inch capacity is 17 cubic inches per inch of box height.

Certifications



File Nbr:
E11461

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com