

Zinc Combination Couplings and Nail Straps

For EMT Conduit and Flexible Metallic Conduit

Application:

A combination coupling to provide a transition from E.M.T. to flexible metallic conduit.

Features:

- Assembled with tri-combo screws

Standard Materials:

Zinc Die Cast




UL Listed:

E198256
CSA File No. LR57925



Type 170C



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
*170C	1/2" E.M.T. - 3/8" Flex	1.280	1.140	50	500	8	51702
171C	1/2" E.M.T. - 1/2" Flex	1.645	1.340	25	250	10	51703
172C	3/4" E.M.T. - 3/4" Flex	1.975	1.535	20	200	15	51704
173C	1" E.M.T. - 1" Flex	2.285	1.700	10	100	26	51705

*EMT TO NM CABLE

Application:

A combination coupling to provide a transition from E.M.T. to flexible metallic conduit.

Features:

- Assembled with tri-combo screws

Standard Materials:

Zinc Die Cast




UL Listed:

E198256
CSA File No. LR57925



Type 171



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
171	1/2" E.M.T. - 1/2" FMC	1.645	1.340	25	250	10	51712
172	3/4" E.M.T. - 3/4" FMC	1.975	1.535	20	200	15	51722

Nail Straps for Threaded Rigid Conduit, IMC and EMT Conduit

Application:

To secure rigid to wooden structure members. Use in place of one hole straps.

Features:


- Tensile strength of Cast Steel is 30% higher than Malleable Iron
- Withstands greater striking force

Standard Materials:

Cast Steel

Standard Finish:

Zinc Plated



Type 360M

CATALOG NUMBER	CONDUIT SIZES		UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
	THINWALL	RIGID				
360M	1/2"	3/8"	100	1000	3	83607
361M	3/4"	1/2"	100	1000	4	83617
362M	1"	3/4"	100	1000	6	83627