

# Zinc Cable and Conduit Connectors

For Armored Cable, Metal Clad and Flexible Metallic Conduit

## Application:

For use with flexible metal conduit and reduced wall flexible metal conduit, metal clad and armored cable. They are used to connect two, Trade Size 3/8 (12) flexible metal conduits, two armored cable of appropriate size marked, or two metal clad cable of appropriate size marked to an enclosure through a Trade Size 1/2 (16) knockout.

## Features:

- UL Listed Locknut
- Male hub NPS
- Tri-combo head screws

## Standard Materials:

Zinc Die Cast



**UL Listed:**

E155411



CSA File No. LR57925

## Application:

Strap-type fitting used to connect flexible metal conduit or armored cable to box or enclosure.

## Features:

- UL Listed Locknut
- Male Hub NPS
- Tri-combo head screws

## Standard Materials:

Zinc Die Cast



**UL Listed:**

E155411



CSA File No. LR57925

## Duplex Single Screw-Clamp Type



Type C270A



CATALOG NUMBER	TRADE SIZE	DIM. A MIN.	DIM. A MAX.	DIM. B	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100	NAED MFG #78-5994 UPC/DCI #
C270A	3/8"	1.688	0.438	1.625	25	250	13	52712


These connectors are used to secure the following cable to an enclosure:

- 0.58 Inch Maximum Diameter Aluminum Armored Cable (10-3)
- 0.48 Inch Minimum Diameter Aluminum Armored Cable (14-2)
- 0.50 Inch Maximum Diameter Steel Armored Cable (10-3)
- 0.46 Inch Minimum Diameter Steel Armored Cable (14-2)
- 0.610 Inch Maximum Diameter Aluminum MCI (10-3)
- 0.468 Inch Minimum Diameter Aluminum MCI (14-2)
- 0.6 Inch Maximum Diameter Steel MCI (10-3)
- 0.47 Inch Minimum Diameter Steel (14-2)
- 0.495 Inch Maximum Diameter Aluminum MCI-A (10-3)
- 0.370 Inch Minimum Diameter Aluminum MCI-A (14-2)
- 0.495 Inch Maximum Diameter Aluminum HCF MCI-A (10-2)
- 0.418 Inch Minimum Diameter Aluminum HCF MCI-A (12-2)
- FMC

## Duplex Two-Screw Clamp Type



Type C270



CATALOG NUMBER	TRADE SIZE	DIM. A	DIM. B	DIM. C	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100	NAED MFG #78-5994 UPC/DCI #
C270	3/8"	1.688	0.438	1.625	20	200	12	52702

These connectors are used to secure the following cable to an enclosure:

- 0.58 Inch Maximum Diameter Aluminum Armored Cable (10-3)
- 0.48 Inch Minimum Diameter Aluminum Armored Cable (14-2)
- 0.50 Inch Maximum Diameter Steel Armored Cable (10-3)
- 0.46 Inch Minimum Diameter Steel Armored Cable (14-2)
- 0.610 Inch Maximum Diameter Aluminum MCI (10-3)
- 0.468 Inch Minimum Diameter Aluminum MCI (14-2)
- 0.6 Inch Maximum Diameter Steel MCI (10-3)
- 0.47 Inch Minimum Diameter Steel (14-2)
- 0.495 Inch Maximum Diameter Aluminum MCI-A (10-3)
- 0.370 Inch Minimum Diameter Aluminum MCI-A (14-2)
- 0.495 Inch Maximum Diameter Aluminum HCF MCI-A (10-2)
- 0.418 Inch Minimum Diameter Aluminum HCF MCI-A (12-2)
- FMC

(718) 259-6100 • Fax: (718) 331-1874 • 1-800-626-1223

www.sepco-usa.com

