

# Power Quality Products Isolated Ground Devices


Twist-Lock® Receptacles




## Isolated Ground Twist-Lock Receptacles

Rating	NEMA Number	NEMA Configuration	Description	Catalog Numbers
15A 125V	L5-15R		2 pole, 3 wire, duplex. 2 pole, 3 wire, single.	<b>IG4700A</b> <b>IG4710</b>
15A 250V	L6-15R		2 pole, 3 wire, duplex. 2 pole, 3 wire, single.	<b>IG4550A</b> <b>IG4560</b>
20A 125V	L5-20R		2 pole, 3 wire, single.	<b>IG2310</b>
20A 250V	L6-20R		2 pole, 3 wire, single.	<b>IG2320</b>
20A 480V AC	L8-20R		2 pole, 3 wire, single.	<b>IG2340</b>
30A 125V	L5-30R		2 pole, 3 wire, single.	<b>IG2610</b>
30A 250V	L6-30R		2 pole, 3 wire, single.	<b>IG2620</b>
20A 125/250V	L14-20R		3 pole, 4 wire, single.	<b>IG2410</b>
20A 3Ø 250V AC	L15-20R		3 pole, 4 wire, single.	<b>IG2420</b>
30A 125/250V	L14-30R		3 pole, 4 wire, single.	<b>IG2710</b>
30A 3Ø 250V AC	L15-30R		3 pole, 4 wire, single.	<b>IG2720</b>
20A 3Ø Y 120/208V AC	L21-20R		4 pole, 5 wire, single.	<b>IG2510</b>
30A 3ØY 120/208V AC	L21-30R		4 pole, 5 wire, single.	<b>IG2810</b>


Note: All receptacles are orange.



**IG4700A**



**IG4710**



**IG2310**

## Power Quality Products Isolated Ground TWIST-LOCK® Receptacles

### Features and Benefits

All-brass mounting and grounding system provides a low resistance ground path.

Insulation barrier construction first patented by Hubbell isolates ground contact from the mounting strap.

Wire restraint recess for both back and side wiring reduces terminal loosening.

High-impact, abuse-resistant nylon face.

Glass-filled thermoplastic polyester base is heat and impact resistant, providing dimensional stability and strength.

Color-coding by voltage rating helps ensure mating of proper devices.

One-piece contact with long spring arm (low stress) and oxide cutting nibs; prevents stress and overheating.


Boss diameter is 1.562" (39.6) on 20 and 30A devices, simplifying installation.

#10 silicon bronze terminal screw provides excellent strength and resistance to corrosion and stripping.

Accommodates both back and side wiring.

External back wiring allows visual inspection of terminations.

Automatic grounding clip assures ground continuity between mounting strap and metal wall box.



Face color-coding by voltage facilitates locating and mating of proper devices.

