

## Dimmers with on/off switch



- **C•L®** dimmers provide reliable dimming of dimmable CFLs/LEDs, as well as halogens and incandescents
- **eco-dim®** model guarantees at least 15% energy savings and triples lamp life compared to a standard switch†

 **Incandescent/halogen dimmers**  
**Dimmable CFL (screw-base) dimmers**  
**Dimmable LED (screw-base) dimmers**

**C•L dimmers**

3-way/single-pole	CTCL-153P- <b>XX</b> <sup>1</sup>
120V 600W (INC) 150W (CFL or LED)	

Visit [www.lutron.com/dimcflled](http://www.lutron.com/dimcflled) for an approved list of dimmable CFL/LED bulbs, and how to calculate wattage when mixing lamp types.

 **Incandescent/halogen dimmers**

**Dimmers**

Single-pole	CT-600P- <b>XX</b> <sup>1</sup>
120V 600W	

3-way	CT-603P- <b>XX</b> <sup>1</sup>
120V 600W	

**eco-dim dimmer†**

Multi-location/single-pole	CT-603PG- <b>XX</b> <sup>2</sup>
120V 600W	

**XX<sup>1</sup>**: Gloss color codes, see pg. 90  
**XX<sup>2</sup>**: Gloss White (WH), Light Almond (LA), Almond (AL) and Ivory (IV), see pg. 90 (Wallplates not included. Order separately, see pg. 169)

 **Incandescent/halogen or**  
 **Magnetic low-voltage dimmers**

**Dimmers**

3-way/single-pole	CT-103P- <b>XX</b> <sup>1</sup>
120V 600VA (1000W)	

The stated VA (Volt-Ampere) rating includes the magnetic transformer heat losses and the lamp load.

The stated W (Watt) rating is the maximum lamp wattage based on assumed 20% transformer loss.

 **Electronic low-voltage dimmers\***

**Dimmers**

3-way/single-pole	CTELV-303P- <b>XX</b> <sup>1</sup>
120V 300W	

Certain LED drivers are dimmable using an ELV dimmer; visit [www.lutron.com/LED](http://www.lutron.com/LED) for more information.

Satin Colors All models must be derated if ganged unless otherwise noted, see pg. 179. For more information on Lutron ballasts, visit [www.lutron.com/ballasts](http://www.lutron.com/ballasts).

**\*Requires neutral wire connection.**

†Maximum light output of 85% guarantees 15% energy savings over standard switches.

### Dimmers with on/off switch and locator light



- Rocker switch returns light to your favorite level
- Slide up to brighten, down to dim
- Includes locator light
- **eco-minder™** green LED demonstrates 15% or more energy savings compared to a standard switch

### Fan controls



- Rocker switch turns on/off
- Slide up to increase speed, down to decrease speed
- 3 quiet fan speeds for increased comfort
- For use with only one ceiling paddle fan
- Designed to prevent motor hum

#### Incandescent/halogen dimmers

##### eco-minder dimmers with locator light

3-way/single-pole	CT-603PI- <b>XX</b> <sup>2</sup>
120V 600W	

#### Fan controls

##### Fan controls—quiet 3-speed

3-way/single-pole	CTFSQ-F- <b>XX</b> <sup>1</sup>
120V 600W	


No derating required if ganged.

**XX**<sup>1</sup>: Gloss color codes, see pg. 90  
**XX**<sup>2</sup>: Gloss White (WH), Light Almond (LA), Almond (AL) and Ivory (IV), see pg. 90 (Wallplates not included. Order separately, see pg. 169)

Satin Colors All models must be derated if ganged unless otherwise noted, see pg. 179.


**Connections overview**

**Load connections\***



**Control types (for 2 or more locations)**

Dim from one location, switch from the others



For more information on ballasts, visit [www.lutron.com/ballasts](http://www.lutron.com/ballasts).

For more information on LED drivers, visit [www.lutron.com/LED](http://www.lutron.com/LED).

**\*For illustration purposes only.**


Consult model number pages for specific voltage and capacity information.

Download complete Connection Diagrams

## Accessories

### Wallplates

4.75 in (121 mm)



Shown actual size:  
2-gang Claro® wallplate  
in White (WH).

For more information  
about Designer wallplates,  
see pg. 169.

4.69 in  
(119 mm)

.30 in  
(7.6 mm)  
profile

### Coordinated electrical devices



Tamper resistant  
GFCI receptacle



Customizable  
6-port frame



Cable jack

For more information  
about coordinated  
Designer electrical  
devices, see pg. 172.