

SNAP²IT[®] MC Cable Connectors

Largest Line. Widest Cable Ranges. Fastest Installation.



**SAVE
17 seconds
per connector**

**LISTED
SNAP²IT[®]
CONNECTORS FOR
NEW MC-PCS CABLE**
...lighting & low voltage
circuits in the
same cable



4010AST
1/2" KO

5010AST
1/2" KO

505010AST
3/4" KO

4110ST

CATALOG NUMBER	UPC/DCI/NAED MFG #01 8997	DESCRIPTION	CABLE OUTSIDE DIA (OD)	UNIT/STD PKG
4010AST	40355	Snap in, 1/2" KO SNAP2IT Type w insulated throat	.405 to .610	50/500
5010AST	00517	Snap in, 1/2" KO SNAP2IT Type w insulated throat	.590 to .920	25/250
505010AST	00520	Duplex Snap in, 3/4" KO SNAP2IT Type w insulated throat	(2) .590 to .920	25/25
4110ST	00728	Snap in, 1/2" KO SNAP2IT Type	.525 to .705	50/500
414110ST	00729	Duplex Snap in, 1/2" KO SNAP2IT Type	(2) .525 to .640	25/100

**In Stock
Available
NOW!**

Arlington's zinc diecast SNAP²IT[®] fittings are the *easiest to insert* snap-on connectors. And they handle the widest variety of cables!

- **Easiest installation**
New and improved design delivers the easiest cable insertion.
- **Widest total cable ranges**
Our Snap²IT[®] connector line accommodates cables from 14/2 to 3/3.
- **Widest variety of cables**
For AC, MC, HCF, MC continuous corrugated aluminum cable, MCI-A cables (steel and aluminum), AC90, ACG90.

These FIVE Snap2it connectors fit the NEW MC-PCS CABLE (lighting and low voltage circuits in same cable) and offer the GREATEST TIME-SAVINGS.

- Super-secure installation in new work or retrofit
- Connector is removable, reusable
- Fully assembled – Ready to use
- Concrete-tight when taped

Easiest cable
insertion.
NO TOOLS!
Secure hold.



Arlington
www.aifittings.com

Check that the cable's outer diameter (OD) listed by the cable manufacturer is within the OD cable range listed for the fitting. The cable jacket should never be able to go through the end stop (of fitting).



SNAP²IT[®] MC Cable Connectors

Largest Line. Widest Cable Ranges. Fastest Installation.

Snap2It Connectors with Insulated Throat and Angled Two-prong Clip

Our 3810AST through 7510AST SNAP²IT[®] connectors install just as fast and cost the same as our other Snap2It fittings, but **cable insertion is even easier!**

- **Easy installation** snap cable into fitting – assembly into box...No tools!
- Angled clip locks onto MC cable – No pullout
- **Removal, reusable**
From cable: Loosen screw on top of connector. Pull cable out.
From box: Slip screwdriver under Snap-Tite ring and twist (photo on back).




4010AST Exploded View/Components

- Screw holds clip permanently in place – Loosen to remove cable
- Angled, two-prong clip locks down on cable, holding it securely in place

Insulated throat




Patented










7510AST Back view

Angled, heavy-duty two-prong clip holds large cables securely in place



LARGER SIZES

CATALOG NUMBER	UPC/DCI/NAED MFG. #01 8997	CABLE (OD) OUTSIDE DIAMETER	CABLE TYPE	CABLE SIZES	UNIT PKG	STD PKG
3810AST 	00385	.370 to .510	For steel and aluminum: MC/HCF/AC NEW MC-PCS MCI-A	14/2 and 12/2 with and w/o ground; 14/3 and 12/3	50	500
		.450 to .480	AC90, ACG90	14/2, 14/3, 12/2, 12/3		
383810AST Duplex 	10937		Flexible metal conduit (regular and reduced wall)	3/8" Flex* .560 to .610	25	100
4010AST 	40355	.405 to .610	For steel and aluminum: MC/HCF/AC NEW MC-PCS	14/2, 14/3, 14/4, 12/2, 12/3, 12/4, 10/2, 10/3	50	500
		.405 to .580	MCI-A			
404010AST Duplex 	40533	.460 to .550	AC90, ACG90	Flexible metal conduit (regular and reduced wall)	25	100
5010AST 1/2" KO 	00517	.590 to .780	For steel and aluminum: MC/HCF/AC NEW MC-PCS	10/3, 10/4, 8/2, 8/3, 8/4, 6/2, 6/3	25	250
		.610 to .780	MCI-A			
		.650 to .850	AC90, ACG90	10/3, 10/4, 8/2, 8/3		
505010AST Duplex 3/4" KO 	50720		Flexible metal conduit (regular and reduced wall)	1/2" Flex* .860 to .920	25	25
7510AST 3/4" KO 	55090	.895 to 1.110	For steel and aluminum: MC/HCF/AC MCI-A	8/4, 6/4, 6/3	25	25
		.900 to .970	AC90	6/3, 4/4, 4/3, 3/3		
			Flexible metal conduit (regular and reduced wall)	3/4" Flex* 1.045 to 1.105		

Check that the cable's outer diameter (OD) listed by the cable manufacturer is within the OD cable range listed for the fitting. The cable jacket should never be able to go through the end stop (of fitting.) *CSA Listed w/ anti-short bushing ONLY

Single (Straight & 90 degree) • Duplex

for New Work and Retrofit

90 Degree Snap2It® Connectors

Arlington's snap in connectors save time by eliminating the multiple steps required for a 90 degree 2-screw connector. **And they COST THE SAME AS A TWO-SCREW, 90 degree connector.**



CATALOG NUMBER	UPC/DCI/NAED MFG #01 8997	CABLE TYPE	CABLE (OD) OUTSIDE DIAMETER	CABLE SIZES	UNIT PKG	STD PKG
38900ST	04098	NEW...MC-PCS CABLE	.405 to .605			
		MC/HCF/AC Steel & Aluminum	.405 to .605	14/2 and 12/2 w/ and w/o ground	25	250
38900AST with insulated throat	04093	MCI-A Steel & Aluminum	.440 to .550	14/3, 14/4, 12/3, 12/4, 10/2, 10/3	25	250
		AC90, ACG90	.440 to .550			
		Flexible Metal Conduit Steel & Aluminum (RWFMC)	3/8" Flex* .560 to .610			


Tinted red inside fitting

CATALOG NUMBER	UPC/DCI/NAED MFG #01 8997	CABLE TYPE	CABLE (OD) OUTSIDE DIAMETER	CABLE SIZES	UNIT PKG	STD PKG
40900ST	04099	NEW...MC-PCS CABLE	.405 to .605			
		MC/HCF/AC Steel & Aluminum	.485 to .610	14/3, 12/2 and 12/3 w/ and w/o ground	25	250
40900AST with insulated throat	04092	MCI-A Steel & Aluminum	.480 to .580	14/4, 12/4, 10/2, 10/3	25	250
		AC90, ACG90	.480 to .550			
		Flexible Metal Conduit Steel & Aluminum (RWFMC)	3/8" Flex* .560 to .610			

*CSA Listed w/ anti-short bushing ONLY



for use in INSTALLED BOXES • RETROFIT



1
Pull MC cable through knockout in **INSTALLED** old work box.

Snap fitting onto cable.



2
Push assembly into box...



3
...snap it into the box.
Fast and easy. No tools required!

Arlington's one-piece **RETROFIT SNAP²IT[®]** fittings are *easy to use in OLD WORK installations*. They're ideal for adding additional circuits to a load center. And you get the same time-savings in a retrofit installation as you do in new work!


Quick, easy installation – NO TOOLS required.

CATALOG NUMBER	UPC/DCI/NAED MFG #01 8997	CABLE TYPE	CABLE (OD) OUTSIDE DIA	CABLE SIZES	UNIT/STD PKG
38RAST with insulated throat	13586	MC/HCF/AC Steel & Aluminum	.405 to .605	14/2 and 12/2 w/ and w/o ground	25
		MCI-A Steel & Aluminum	.440 to .550	14/3, 14/4, 12/3, 12/4, 10/2, 10/3	
		AC90, ACG90	.440 to .550		
		Flexible Metal Conduit Steel & Aluminum (RWFMC)	3/8" Flex* .560 to .610		
40RAST with insulated throat Tinted RED inside fitting	13587	MC/HCF/AC Steel & Aluminum	.485 to .610	14/3, 12/2 and 12/3 w/ and w/o ground	25
		MCI-A Steel & Aluminum	.480 to .580	14/4, 12/4, 10/2, 10/3	
		AC90, ACG90	.480 to .550		
		Flexible Metal Conduit Steel & Aluminum (RWFMC)	3/8" Flex* .560 to .610		

*CSA Listed w/ anti-short bushing ONLY



Check that the cable's outer diameter (OD) listed by the cable manufacturer is within the OD cable range listed for the fitting. The cable jacket should never be able to go through the end stop (of fitting.)



Arlington
www.aifittings.com

SNAP²IT[®] MC Cable Connectors

for NEW WORK

Snap2It[®] Connectors

Designed for new construction, this SNAP²IT[®] series offers quick, easy snap-in installation into cable and into box. NO TOOLS required.


SAVE ^{about} 17 seconds per connector!

CATALOG NUMBER	UPC/DCI/NAED MFG #01 8997	CABLE TYPE	CABLE (OD) OUTSIDE DIA	CABLE SIZES	UNIT/STD PKG
* WITH INSULATED THROAT					
		NEW...MC-PCS CABLE	.405 to .612	14/2 and 12/2	25
38AST *	00070	MC/HCF/AC Steel & Aluminum	.405 to .612	w/ and w/o ground	25
380ST	00381	MCI-A Steel & Aluminum	.405 to .612	14/3, 14/4,	25
380AST *	00382	AC90, ACG90 Flexible Metal Conduit	.405 to .612	12/3, 12/4,	25
		Steel & Aluminum (RWFMC)	.560 to .610	10/2, 10/3	
WITH INSULATED THROAT, TINTED RED INSIDE OPEN TANG DESIGN					
		NEW...MC-PCS CABLE	.485 to .610	14/3, 12/2 and 12/3	
40AST	00041	MC/HCF/AC Steel & Aluminum	.485 to .612	w/ and w/o ground	25
400AST	40347	MCI-A Aluminum	.485 to .612	14/4,	25
		AC90, ACG90 Flexible Metal Conduit	3/8" Flex**	12/4,	
		Steel & Aluminum (RWFMC)	.560 to .610	10/2, 10/3	

**Flex CSA Listed w/ anti-short bushing ONLY




1 Snap fitting onto cable... twist clockwise



2 ...snap assembly into the box!

EASY TO INSTALL

EASY TO REMOVE and REUSE...



To remove from box, lift Snap-Tite[®] ring with a screwdriver and twist off.

PRODUCT COMPARISON



RED TINT inside means OPEN TANG Design


More room inside for easy insertion of wires...redesigned snap ring makes it easier than ever to snap fitting into box



38AST



40AST RED Tint inside



Check that the cable's outer diameter (OD) listed by the cable manufacturer is within the OD cable range listed for the fitting. The cable jacket should never be able to go through the end stop (of fitting.)

Arlington

1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com

Patented ©2015 Arlington 0415_100/25M

DISTRIBUTED BY

