

FLEXIBLE AND PORTABLE CORD

Jumper Cable - 5 kV/15kV
Transformer Lead Wire
Non-Shielded - 90°C



CONSTRUCTION	
Conductor	• Bare annealed copper
Strand Shield	• Extruded Semi-Conducting Compound
Insulation	• EPR per ICEA S-96-659
Jacket	• EPDM rubber

Applications:

- Used as flexible power lead for temporary connections from phase to phase in voltages from 5 KV to 15 KV

Part #	AWG	Conductors	Stranding	Nominal O.D. over Conductor	Nom. O.D.	Lbs./M'
B40201	2	1	259	.330"	.775"	492
B41/001	1/0	1	259	.420"	.865"	580
B42/001	2/0	1	259	.474"	.920"	738
B44/001	4/0	1	516	.540"	.985"	1017
B435001	350	1	855	.775"	1.240"	1487
B450001	500	1	1235	.930"	1.395"	2087

*Fittings are available for these products.

Note: The data shown are approximate and subject to standard industry and manufacturer tolerances.