


Low Voltage Brackets

Steel

- Eliminates the need for an electrical box when installing low voltage Class 2 wiring
- For old work or new work
- Installs easily with a drywall saw and screwdriver



| Cat. No. | Description |
|--------------------------------------|---|
| Low Voltage Mounting Brackets | |
| CIMB-0 | Flat mounting brackets that provides quick installation of low voltage class 2 communication outlets Positioning tabs ensure straight installation |
| CIMB-1 | Mounting bracket that provides quick installation of low voltage class 2 communication outlets. Raised 1/2 in. Positioning tabs ensure straight installation |
| CICSB-1 | Mounting brackets that provides quick installation of low voltage communication outlets May be used with all 2-1/2 in. deep gangable boxes |
| WBF-1 | Low voltage wall bracket |



| Cat. No. | Dimensions (in.) | | Hole Size (in.) | Suggested Application |
|--|------------------|----------|-----------------|---|
| | H | W | | |
| Nailing Straps (Zinc Plated Steel) | | | | |
| CI1544 | 0.25 | 0.51 | - | 14/2-12/2 |
| Nailing Straps (Polyethylene) | | | | |
| CI1544-P | 0.25 | 0.49 | - | 14/2-12/2 |
| CI1546-P | 0.25 | 0.75 | - | 14/2-8/2 |
| Cable Staples (Galvanized Steel) | | | | |
| CIS-1 | 0.25 | 0.48 | - | 14/2-12/2 |
| CIS-2 | 0.44 | 0.54 | - | 2 cables 14/2; 2 cables 12/2 14/2-14/3-12/2-12/3-10/2-10/3 |
| CIS-3 | 0.49 | 0.70 | - | 10/2-8/2; 14/3-10/3 |
| CIS-4 | 0.76 | 0.86 | - | 8/3-6/3 |
| Double Cable Staples (Galvanized Steel) | | | | |
| CIS-1X2 | 0.25 | 0.48 x 2 | - | 14/2-12/2 |
| CIS-1X2-FP3 | | | | |
| CIS-1X2-FP5 | | | | |







Low Voltage Brackets

Nonmetallic

| | | |
|---|---|---|
|  |  |  |
| SC100A | SC200A | SC300A |

Open-backed to easily accommodate the bend radiuses required for low voltage cabling and deep devices such as volume controls, and is designed to fit a standard two-gang three-gang faceplate. It also features an easy nail-on mounting or screw-in bracket, while more hard shell provides increased durability and no racking.

| | | | |
|--|--|---|--|
|  |  |  |  |
| SC100RR | SC200RR | SC100SC | SC100ADJC |

Swing arm rework bracket. 1 gang.

Swing arm rework bracket. 2 gang.

This low voltage bracket provides a low voltage outlet next to a previously installed high voltage outlet. For new construction and rework. Attaches easily to most electrical boxes, and is designed to fit a standard two-gang faceplate.

New work adjustable low voltage bracket. 1 gang.



| Cat. No. | Description |
|--|--|
| Low Voltage Brackets | |
| SC100A | One-Gang backless bracket 2.32 in. W x 3.73 in. L |
| SC200A | Two-Gang backless bracket 5.35 in. W x 3.81 in. L |
| SC300A | Three-Gang backless bracket 8.69 in. W x 7.20 in. L |
| Old Work Backless Brackets | |
| SC100RR | One-Gang backless old work bracket w/ swing clamps 2-1/4 in. x 3-1/4 in. |
| SC200RR | Two-Gang backless old work bracket w/ swing clamps 3.92 in. x 4.00 in. |
| Low Voltage Add-On Bracket | |
| SC100SC | One-Gang Add-On Bracket 1.80 in. W x 3.68 in. L |
| One-Gang and Two Gang – Low Voltage | |
| SC100ADJC | One-Gang adjustable brackless bracket 3-7/8 in. W x 3-3/4 in. H |
| SC200ADJC | Two-Gang adjustable brackless bracket 5-5/8 in. W x 3-5/8 in. H |

CSA not applicable