



# PL-T Triple 4-Pin Base

## PL-T 26W/835/A/4P/ALTO

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

### Product data


General Information		LLMF 12000 h Rated	
Cap-Base	GX24Q-3 [ GX24q-3]		81 %
LSF Preheat 2000 h Rated	99 %	<b>Operating and Electrical</b>	
LSF Preheat 4000 h Rated	98 %	Power (Rated) (Nom)	27.0 W
LSF Preheat 6000 h Rated	97 %	Lamp Current (Nom)	0.335 A
LSF Preheat 8000 h Rated	90 %	<b>Temperature</b>	
<b>Light Technical</b>		Design Temperature (Nom)	28 °C
Color Code	835 [ CCT of 3500K]	<b>Controls and Dimming</b>	
Initial lumen (Nom)	1750 lm	Dimmable	Yes
Luminous Flux (Rated) (Nom)	1750 lm	<b>Mechanical and Housing</b>	
Color Designation	White (WH)	Cap-Base Information	4P
Chromaticity Coordinate X (Nom)	412	<b>Approval and Application</b>	
Chromaticity Coordinate Y (Nom)	402	Energy Efficiency Label (EEL)	B
Correlated Color Temperature (Nom)	3500 K	Mercury (Hg) Content (Nom)	1.4 mg
Luminous Efficacy (rated) (Nom)	64.8 lm/W	<b>Product Data</b>	
Color Rendering Index (Nom)	82	Order product name	PL-T 26W/835/A/4P/ALTO
LLMF 2000 h Rated	92 %		
LLMF 4000 h Rated	88 %		
LLMF 6000 h Rated	85 %		
LLMF 8000 h Rated	84 %		

## PL-T Triple 4-Pin Base

EAN/UPC - Product	046677268244
Order code	458265
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	927910983550

Net Weight (Piece)	64.000 g
ILCOS Code	FSM-26/35/1B-E-GX24q=3

### Dimensional drawing



PL-T ALTO 26W/835/4P A

Product	D	A	B	C
PL-T 26W/835/A/4P/ALTO	41 mm	86.7 mm	111.0 mm	126.7 mm

