







**Life Safety
Portfolio**

Commercial and Industrial Life Safety Luminaires



Commercial Indoor Emergency Lights, Exits and Combos

Lithonia Lighting® emergency lighting products continue to prove reliable and affordable. With a low-profile form factor and small, unobtrusive LED lamp heads, the commercial indoor emergency lights, exit signs and exit combination lights are designed to remain inconspicuous in small spaces at low mounting heights while providing 90-minutes of illumination upon the loss of AC power.

	EU2L*	EU2C	ELM2L	ELM4L & ELM6L
				
Controls	No	No	SDRT - Self-Diagnostics and Remote Testing	SDRT - Self-Diagnostics and Remote Testing
Key Features & Options	<ul style="list-style-type: none"> White housing Black housing REM - Remote Capacity 	<ul style="list-style-type: none"> White housing Black housing HO - High Output Option SD - Self Diagnostic Option 	<ul style="list-style-type: none"> White housing Black housing Linear pattern LED Fixed optics WPVS - Wet Protective Vandal Shield Option Multiple remotes options USPOM - Assembled in the US Option 	<ul style="list-style-type: none"> White housing Black housing WPVS - Wet Protective Vandal Shield Option Multiple remotes options LLH - Less Lamp Heads Option HO - High-Output Battery Option EHO - Extra High-Output Battery Option USPOM - Assembled in the US Option PM - Pendant Mount Option
Standard Voltage	Dual-voltage input (120/277V)	Dual voltage input (120V/277V)	Dual voltage input (120/277V) or UVOLT (120-347V)	Dual voltage input (120/277V) or UVOLT (120-347V)
Lamp	LED	LED	220 lumen LED	640 lumen LED (ELM4L) 1,100 lumen LED (ELM6L)
Construction	Thermoplastic housing	Thermoplastic housing	Thermoplastic housing Acrylic lens	Polycarbonate housing Acrylic lens
UL & Other Ratings	UL 924, NFPA 101, IBC and NFPA 70-NEC <small>UL listed. Certified in CA T20 Appliance Efficiency Database</small>	UL 924, NFPA 101, IBC, NFPA-70 NEC, FCC and OSHA <small>UL listed. Certified in CA T20 Appliance Efficiency Database</small>	UL 924, NFPA 101, IBC, NFPA 70, NOM, FCC and OSHA <small>Certified in CA T20 Appliance Efficiency Database</small>	UL 924, NFPA 101, IBC, NFPA 70, NOM, FCC and OSHA <small>Certified in CA T20 Appliance Efficiency Database</small>
Temperature Range	50-104°F (10-50°C)	50-104°F (10-40°C)	50-104°F (10-40°C)	50-104°F (10-50°C)
Battery	Nickel-cadmium	Nickel-cadmium	Nickel-cadmium, Lithium iron phosphate (LTP)	Nickel-cadmium, Lithium iron phosphate (LTP)
Spacing	Up to 18 - feet	Up to 14 - feet	Up to 33 - feet	Up to 98 - feet (ELM6L)
Light Pattern	Narrow	Narrow	Spot	Spot
Emergency Power	90 - minutes	90 - minutes	90 - minutes	90 - minutes
Installation	Ceiling- or wall-mount	Wall-mount only	Ceiling- or wall-mount	Ceiling- or wall-mount
Self-Diagnostics (optional)	No	Yes	Yes	Yes

*Some versions are part of the Contractor Select Program and In Stock

	EX LED EL*	LQM (EL N)	ECC Combo*	LHQM LED	WLTC
	LED Exit Emergency		LED Exit Emergency Combo		Wet Location LED Emergency Combo
					
Controls	No	Self-Diagnostics	No	Self-Diagnostics	Self-Diagnostics
Key Features & Options	<ul style="list-style-type: none"> ▪ White housing ▪ Black housing ▪ Red panel ▪ Green panel ▪ Single face ▪ Double face ▪ Wireguard ▪ Extra faceplate for field-conversion standard 	<ul style="list-style-type: none"> ▪ White housing ▪ Red panel ▪ Green panel ▪ Test switch ▪ Status Indicator ▪ Rechargeable battery ▪ SD - Self Diagnostics ▪ SDFIFA 	<ul style="list-style-type: none"> ▪ White housing ▪ Black housing ▪ Red panel ▪ Green panel ▪ REM - Remote Capacity ▪ SPV - 120/230V 50/60Hz 	<ul style="list-style-type: none"> ▪ White housing ▪ Black housing ▪ Red panel ▪ Green panel ▪ LLH - Less Lamp Heads Option ▪ HO - High-Output Battery Option ▪ Salida signage (non-UL) 	<ul style="list-style-type: none"> ▪ White housing ▪ Black housing ▪ Single face ▪ Double face ▪ Red panel ▪ Green panel ▪ TPS - Tamperproof Screw Hardware Option ▪ SD - Self Diagnostics Option ▪ CW - Cold Weather Option
Standard Voltage	Dual-voltage input (120/277V)	Dual-voltage input (120/277V)	Dual voltage input (120/227V)	Dual-voltage input (120/277V)	Dual-voltage input (120/277V)
Lamp	LED	LED	LED	LED	220 Lumens LED, 3.6 watt
Construction	Thermoplastic housing	Thermoplastic housing	Thermoplastic housing	Thermoplastic housing	Polycarbonate housing Clear polycarbonate lens
UL & Other Ratings	UL 924, NFPA 101, IBC, NFPA 70-NEC and OSHA Indoor damp location listed standard	UL924, NFPA 101, IBC, OSHA and NOMI Certified UL damp location listed standard, Meets all applicable FCC requirements	UL 924, NFPA 101, IBC and NFPA 70-NEC Indoor damp location listed	UL 924, NFPA 101, IBC, NEC and OSHA UL damp location listed	UL 924, NFPA 101, IBC and NFPA-NEC UL listed. Wet location listed
Temperature Range	50-104°F (10-40°C)	50-104°F (10-40°C)	50-104°F (10-40°C)	50-104°F (10-40°C)	32-122°F (0-50°C) CW -4-122°F (-20-50°C)
Battery	Nickel-cadmium	Nickel-cadmium	Nickel-cadmium	Nickel-cadmium	Nickel-cadmium
Spacing	N/A	N/A	Up to 18 - feet	Up to 24 - feet (single) Up to 25 - feet (multiple)	24 - feet +
Light Pattern	N/A	N/A	N/A	N/A	Spot
Emergency Power	90 - minutes	90 - minutes	90 - minutes	90 - minutes	90 - minutes
Installation	Universal (top, end or back) mount	Universal (top, end or back) mount	Universal (top, end or back) mount	Universal (top, end or back) mount	Universal (top, end or back) mount
Self-Diagnostics (optional)	No	Yes	No	Yes	Yes

*Some versions are part of the Contractor Select Program and In Stock




Emergency Remote Light Heads

The Lithonia Lighting® emergency remote lights provide an economical option for design continuity of emergency lighting. They are available with single and twin LED remote lamp heads for indoor and outdoor applications, for use as part of an emergency lighting system, providing light for path of egress.

	INDRE	EXTLRE	ELMRE
	Light and Demanding Environments	Heavy and Demanding Environments	Indoor
			
Controls	N/A	N/A	N/A
Key Features & Options	<ul style="list-style-type: none"> ■ Single/Twin lamps ■ Gray housing 	<ul style="list-style-type: none"> ■ Single/Twin lamps ■ Gray housing 	<ul style="list-style-type: none"> ■ Single/Twin/ FXO Fixed lamps ■ Black housing ■ White housing ■ WPVS - Wet Protective Vandal Shield Option
Standard Voltage	Universal DC (7-30VDC)	Universal DC (7-30VDC)	Universal DC (5-30VDC)
Lamp	<ul style="list-style-type: none"> ■ SP640L 640 lumen, 3.3 watt ■ SP1100L 1100 lumen, 5.3 watt ■ SP2200L 2200 lumen, 11 watt 	<ul style="list-style-type: none"> ■ SP640L 640 lumen, 3.3 watt ■ SP1100L 1100 lumen, 5.3 watt ■ SP2200L 2200 lumen, 11 watt 	<ul style="list-style-type: none"> ■ LP220L 220 lumen, 2.4 watt ■ SP640L 640 lumen, 6.6 watt ■ SP1100L 1100 lumen, 10.6 watt
Construction	Die-cast aluminum housing	Die-cast aluminum housing, Clear polycarbonate cover	Thermoplastic housing Acrylic lens
UL & Other Ratings	UL 924, NFPA 101, IBC, NFPA 70 (NEC), NOM, FCC and OSHA <small>UL Wet location listed standard, List and labeled to comply with Canadian Standards C22.2 No. 141-10, Certified in CA T20 Appliance Efficiency Database</small>	NEMA 4X, IP66 and NSF, UL 924, NFPA 101, IBC, NFPA 70 (NEC), NOM, FCC and OSHA <small>UL Wet location listed standard, List and labeled to comply with Canadian Standards C22.2 No. 141-10, Certified in CA T20 Appliance Efficiency Database</small>	UL 924, NFPA 101, IBC, NFPA 70, NOM, FCC, OSHA <small>Certified in CA T20 Appliance Efficiency Database, List and labeled to comply with Canadian Standards C22.2 No.141-10</small>
Temperature Range	-22-122°F (-30 - 50°C)	-22-122°F (-30-50°C)	50-104°F (10 - 40°C) (5Vdc - 30Vdc) -22-104°F (-30 - 40°C) (7Vdc - 30Vdc)
Battery	N/A	N/A	N/A
Spacing	Up to 130 - feet	Up to 130 - feet	Up to 98 - feet (SP1100L)
Light Pattern	Spot	Spot	Linear/Spot
Emergency Power	90 - minutes	90 - minutes	90 - minutes
Installation	Wall-mount	Wall-mount	Ceiling- or wall-mount
Self -Diagnostics (optional)	N/A	N/A	N/A

Industrial, Outdoor and Architectural Emergency Lights

The Lithonia Lighting® demanding environment emergency lights are perfectly suited for industrial, manufacturing, commercial and municipal applications. The rugged designs target light, heavy and demanding, indoor and outdoor environments. With superior-performance lamp heads, these luminaires are ideally suited for maximum spacing at higher mounting heights.

	INDL	EXTL	AFF	AFB	AFO
	Heavy and Demanding LED Emergency Lights		Indoor/Outdoor LED Emergency Lights		
					
Controls	N/A	N/A	Optional normally-off or normally-on with photocell	Optional normally-off or normally-on with photocell	Normally-on with photocell
Key Features & Options	<ul style="list-style-type: none"> ■ Gray housing ■ SDRT - Self-Diagnostic Remote Testing ■ HO - High-Output Battery ■ EHO - Extra High-Output Battery ■ CW - Cold Weather ■ Matching remotes 	<ul style="list-style-type: none"> ■ Gray housing ■ SDRT - Self-Diagnostic Remote Testing ■ HO - High-Output Battery ■ EHO - Extra High-Output Battery ■ CW - Cold Weather ■ Matching remotes 	<ul style="list-style-type: none"> ■ White housing ■ Dark bronze housing ■ Black housing ■ Silver housing ■ SDRT - Self-Diagnostic Remote Testing ■ Matching remotes 	<ul style="list-style-type: none"> ■ White housing ■ Dark bronze housing ■ SDRT - Self-Diagnostic Remote Testing ■ Matching remotes 	<ul style="list-style-type: none"> ■ White housing ■ Dark bronze housing ■ Self-Diagnostic Testing
Standard Voltage	120-347 VAC, 50/60hz	120-347 VAC, 50/60hz	120-347 VAC, 50/60Hz	120-347 VAC, 50/60Hz	120-277 VAC, 50/60Hz
Lamp	<ul style="list-style-type: none"> ■ SP640L 640 lumen LED, 3.3 watt ■ SP1100L 1100 lumen LED, 5.3 watt ■ SP2200L 2200 lumen LED, 11 watt 	<ul style="list-style-type: none"> ■ SP640L 640 lumen LED, 3.3 watt ■ SP1100L 1100 lumen LED, 5.3 watt ■ SP2200L 2200 lumen LED, 11 watt 	<ul style="list-style-type: none"> ■ 635 Lumens LED (EM) ■ 635 Lumens LED (Normal on) ■ 4,000 CCT 	<ul style="list-style-type: none"> ■ 225 Lumens LED (EM) ■ 225 Lumens LED (Normal on) ■ 4,000 CCT 	<ul style="list-style-type: none"> ■ 350 Lumens LED (EM) ■ 1275 Lumens LED (Normal on) ■ 5,000 CCT
Construction	Polycarbonate housing	Polycarbonate housing	Die-cast aluminum housing Polycarbonate lens	Die-cast aluminum housing Polycarbonate lens	Die-cast aluminum housing Polycarbonate lens
UL & Other Ratings	UL 924, NFPA 101, NFPA 70 (NEC), NOM, FCC and OSHA UL damp location listed standard, cUL listed and labeled to comply with Canadian Standards C22.2 No. 141-10, Certified in CAT20 Appliance Efficiency Database	NEMA 4X, IP66 and NSF, UL 924, NFPA 101, NFPA 70 (NEC), NOM, FCC and OSHA UL damp location listed standard, cUL listed and labeled to comply with Canadian Standards C22.2 No. 141-10, Certified in CAT20 Appliance Efficiency Database	UL 924, NFPA 101, NFPA 70-NEC, C22.2 CSA, FCC and OSHA UL damp location listed standard, cUL listed and labeled to comply with Canadian Standards C22.2 No. 141-10, Certified in CAT20 Appliance Efficiency Database	UL 924, NFPA 101, NFPA 70-NEC, C22.2 CSA, FCC and OSHA UL damp location listed standard, cUL listed and labeled to comply with Canadian Standards C22.2 No. 141-10, Certified in CAT20 Appliance Efficiency Database	UL 924, NFPA 101, NFPA 70-NEC, C22.2 CSA, FCC and OSHA UL damp location listed standard, Certified in CAT20 Appliance Efficiency Database
Temperature Range	32-122°F (0-50°C) CW -22-122°F (-30-50°C)	32-122°F (0-50°C) CW -22-122°F (-30-50°C)	32-122°F (0-50°C) CW -22-122°F (-30-50°C)	32-122°F (0-50°C) CW -22-122°F (-30-50°C)	32-122°F (0-50°C) CW -22-122°F (-30-50°C)
Battery	Lithium iron phosphate (LTP)	Lithium iron phosphate (LTP)	Lithium iron phosphate (LTP)	Nickel-cadmium, Optional lithium iron phosphate (LTP)	Nickel-cadmium
Spacing	Up to 130 - feet	Up to 130 - feet	Up to 70 - feet	Up to 30 - feet	Up to 30 - feet
Light Pattern	Spot	Spot	Field-adjustable throw Wide throw	Wide throw	Wide throw
Emergency Power	90 - minutes	90 - minutes	90 - minutes	90 - minutes	90 - minutes
Installation	Wall- or pole-mounting	Wall- or pole-mounting	Wall- or building-mounting	Wall- or building-mounting	Wall- or building-mounting
Self-Diagnostics	Yes	Yes	Yes	Yes, optional	Yes



Acuity Brands Life Safety Solutions

Acuity Brands innovative and reliable emergency lighting solutions deliver crucial Life Saving functionality to your interior and exterior building applications.

With innovative technology, high performance LEDs and emergency batteries our Life Safety solutions are designed to exceed code, save time, money and provide peace of mind. All backed by trusted brands Lithonia Lighting, Power Sentry and Iota.



Visit www.lithonia.com for more information